FD3-AR036J00U00P8



Mini FDH 3000 Fiber Distribution Hub, 72-fiber shell, 36 fibers loaded, SC /APC, distribution pigtails, feeder pigtails

Product Classification

Regional Availability	North America	
Product Type	Fiber distribution hub	
Product Series	FDH 3000	
Warranty	One year	
General Specifications		
Access	Front	
Cable Type	Pigtails - Loose Tube	
Color	Putty white	
Distribution Cables, quantity	3	
Distribution Ports, quantity	72	
Fibers per Distribution Cable, quantity	12	
Fibers per Feeder Cable, quantity	8	
Interface, Input	SC	
Interface Feature, Input	APC	
Mounting	Pole Wall	
Splitter Slots, quantity	4	
Dimensions		
Height	482.6 mm 19 in	
Width	330.2 mm 13 in	
Depth	203.2 mm 8 in	
Enclosure Size	Mini	
Material Specifications		
Finish	Powder coated	
Material Type	Aluminum	

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 10, 2024



FD3-AR036J00U00P8

Environmental Specifications

Environmental Space

Aerial

Packaging and Weights

Packaging quantity


Packaging Type

Pallet

1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted
50	



Warranty

For more information, please consult our Product Warranty guidelines

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 10, 2024

