



XAGA™ FOSC™ A1 Fiber Optic Splice Closure, Heat Shrink Cable sealing, complete kit with one pre-installed 12-splice tray, with cable blocking

OBSOLETE

This product was discontinued on: June 30, 2022

Product Classification

Regional Availability	Latin America North America
Product Type	In-line, round fiber closure
Product Brand	FOSC® XAGA®
Product Series	XAGA FOSC

General Specifications

Cable Blocking Components	Included
Cable Ports Quantity, total	2 round ports
Cable Sealing Type	Heat shrink
Closure Sealing Type	Wraparound sleeve
Closure Style	In-line
Color	Black
Network Area Type	Distribution
Splice Tray Included, quantity	1
Splice Tray Type Included	12-way, heat shrink
Splicing Type, Supported	Single fusion

Dimensions

Length	711.2 mm 28 in
Diameter	134.62 mm 5.3 in

010647-000 | XAGA-FOSC-A1-CB

Main Cable Diameter, maximum 25 mm | 0.984 in

Material Specifications

Material Type Fiber-reinforced multi-layer sealing sleeve

Environmental Specifications

Environmental Space Below ground | Buried

Packaging and Weights

Packaging quantity 1

Packaging Type Box | Carton

Weight, net 1 kg | 2.205 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

