



FOSC™600 D Fiber Optic Splice Closure, Gel Cable sealing, butt type, no pre-installed trays, two 3-port gel blocks, 2 ground feedthrough lugs, with test valve

- Single-ended or in-line, gel-sealed closure for splicing feeder and distribution cables
- Excellent consolidation or rehabilitation closure with large fiber splicing capacity
- Compatible with most common cable types: e.g. loose tube, central core, ribbon fiber
- FOSC splice trays hinged for access to any splice without disturbing other trays
- Closure can be used in aerial, pedestal and underground (up to 5 meters) environments
- Compatible with CommScope's CWDM modules and optical splitter trays

Product Classification

Regional Availability	Latin America North America
Product Type	In-line, rectangular fiber closure Single-ended, rectangular fiber closure
Product Brand	FOSC™
Product Series	FOSC 600

General Specifications


Cable Entry Drop Port Style	Gel block
Cable Entry Main Port Style	Gel block
Cable Ports, quantity	6
Cable Sealing Type	Compressed gel
Closure Sealing Type	Captured bolts Over-centered latches with rubber gasket
Closure Style	In-line Single-ended
Color	Black
Mounting	Pole Strand Wall
Network Area Type	Feeder Trunk
Splice Tray Included, quantity	0
Splicing Capacity, Mass Fusion, maximum	1728
Splicing Capacity, Single Fusion, maximum	864
Splicing Capacity, Single Splice, 12 fibers, maximum	864
Splicing Capacity, Single Splice, 6 fibers, maximum	324
Splicing Type, Supported	Mass fusion Single fusion

358924-000 | FOSC600-D6B-NT-0-N2V

Dimensions

Height	254 mm 10 in
Width	274 mm 10.787 in
Length	828 mm 32.598 in
Main Cable Diameter, maximum	35 mm 1.378 in

Ordering Tree



Material Specifications

Material Type	Rugged polymer
----------------------	----------------

Environmental Specifications

Environmental Space	Below ground Buried
Qualification Standards	Telcordia GR-771-CORE, 20 ft waterhead
Water Resistance	Flash test valve at 5 psi (40 kPa)

Packaging and Weights

Packaging quantity	1
---------------------------	---

358924-000 | FOSC600-D6B-NT-0-N2V

Packaging Type

Box | Carton

Weight, net

11.79 kg | 25.992 lb

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS

Classification

Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

