489476-000 | FIST-GC02-BD6-GV



FIST® GCO2 Fiber Optic Splice Closure, Heat Shrink or Gold Gel Cable sealing, size BD, 6 round ports + 1 oval port, with test valve

- Single-ended, O-ring sealed dome closure for splicing feeder and distribution cables
- Compatible with most common cable types: e.g. loose tube, central core, ribbon fiber
- Universal mounting system (UMS) profiles provide foundation for mounting combinations of FIST splice trays
- Closure can be used in aerial, pedestal and underground (up to 5 meters) environments
- Compatible with CommScope's CWDM modules and optical splitter trays

Product Classification

Regional Availability EMEA		
Product Type	Single-ended, round fiber closure	
Product Brand	FIST®	
Product Series	FIST-GC02	
General Specifications		
Cable Entry Drop Port Style	Round	
Cable Entry Main Port Style	Oval	
Cable Ports Quantity, total	1 oval port (2 cables) + 6 round ports	
Cable Sealing Type	Gel kit (optional) Heat shrink	
Closure Sealing Type	Dome-to-base clamp with O-ring	
Closure Style	Single-ended	
Color	Black	
Flash Test Valve	Pre-installed	
Ground Feed-through	Included	
Mounting	Pole Strand Wall	
Network Area Type	Distribution	
Splice Tray Included, quantity	0	
Splice Tray Type Included	No trays	
Splicing Capacity, Mass Fusion, maximum	1440	
Splicing Capacity, Single Fusion, maximum	960	
Splicing Type, Supported	Mass fusion Single fusion	

Page 1 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 22, 2024




489476-000 | FIST-GC02-BD6-GV

Dimensions

Length	566 mm 22.283 in
Cable Entry Drop Port Diameter	30 mm (1.18 in) mm
Diameter	247 mm 9.724 in
Diameter, with clamp	285 mm 11.22 in
Main Cable Diameter, maximum	25 mm 0.984 in

Dimension Drawing



	FIST-GCO2-B <u>C</u>	FIST-GCO2-B <u>D</u>	FIST-GCO2-B <u>E</u>	FIST-GCO2-B <u>F</u>
Length L	488 mm/19.213 in	566 mm/22.283 in	680 mm/26.772 in	795 mm/31.30 in
Width D at base	247 mm/9.724 in	247 mm/9.724 in	247 mm/9.724 in	247 mm/9.724 in
Width D at base with clamp	285 mm/11.22 in	285 mm/11.22 in	285 mm/11.22 in	285 mm/11.22 in

Port Configuration

	Cables per port	Cable Diameter, min	Cable Diameter, max
1 Oval Port	2	12 mm / 0.472 in	25 mm / 0.984 in
6 Round Ports	1	5 mm / 0.197 in	30 mm / 1.181 in

Splicing Configuration


©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 22, 2024



489476-000 | FIST-GC02-BD6-GV

	FIST-GCO2-B <u>C</u>	FIST-GCO2-BD	FIST-GCO2-B <u>E</u>	FIST-GCO2-B <u>F</u>
UMS Units	2x28	2x42	2x58	2x64
# SC/SLE 4mm trays	56	80	112	128
# SE 8mm trays	28	40	56	64
# R12 12mm Flat ribbon trays	18	26	36	42
Max single splice capacity SC trays (4F/tray)	224	320	448	512
Max single splice capacity SE trays (12F/SE)	336	480	672	768
Max single splice capacity High dense tray (12F/SLE)	672	960	1344	1536
Max mass splice capacity R12 trays (Flat ribbon)	432	624	864	1008
Max mass splice capacity SE trays (Rollable ribbon G657A2 fiber)	1008	1440	1728	1728

Ordering Tree



Material Specifications

Material Type

Packaging Type

Round ports

Impact-resistant polymer

Environmental Specifications

(8 : ø 20) + 1 oval port (8 : ø 13.5)

Below ground Buried
IEC 61300, 5 m waterhead
Flash test valve at 5 psi (40 kPa)
1

Box | Carton

Page 3 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 22, 2024



489476-000 | FIST-GC02-BD6-GV

Weight, net

3.9 kg | 8.598 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 22, 2024

