



T2C Copper Closure, unpressurized, gel sealed, in-line, for up to 300 pair splices

- Watertight splice closure for aerial, underground and direct buried splices in the unpressurized copper telecommunication network
- Fast and easy installation and re-entry process with the gel-sealing system
- Robust and reliable under a wide variety of environmental conditions

## OBSOLETE

This product was discontinued on: June 30, 2022

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Product Type</b>	Gel sealed closure
<b>Product Series</b>	T2C

## General Specifications

<b>Application</b>	For use with Polyethylene cables
<b>Cable Capacity, maximum</b>	4
<b>Cable Sealing Type</b>	Gel filled
<b>Closure Style</b>	In-line
<b>Color</b>	Black
<b>Splicing Capacity, maximum</b>	300

## Dimensions

<b>Height</b>	165.6 mm   6.52 in
<b>Width</b>	159.4 mm   6.276 in
<b>Length</b>	695 mm   27.362 in
<b>Sheath Opening, nominal</b>	450 mm   17.717 in

## Environmental Specifications

<b>Environmental Space</b>	Aerial   Buried
----------------------------	-----------------

## Packaging and Weights

<b>Included</b>	Cleaning tissues   Gel sealing tape   Measuring tape   Mounting hardware   O-ring seal   Tie wraps
<b>Packaging quantity</b>	1
<b>Packaging Type</b>	Bag   Carton

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

