

FL2-96SPNL2

FL2000 Fiber Splice Panel, unloaded, for 96 splices, 19 in, 4RU, putty white

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber splice panel
Product Series	FL2000

General Specifications

Functionality	Splicing
Cable Exit Location	Rear, left side Rear, right side
Color	Putty white
Growth Configuration	Unloaded
Interface, front	Unloaded
Rack Type	EIA 19 in
Rack Units	4
Shelf Movement	Hinged
Splicing Capacity, maximum	96
Total Ports, quantity	0

Dimensions

Height	177.8 mm 7 in
Width	482.6 mm 19 in
Depth	256.54 mm 10.1 in

Material Specifications

Finish	Powder coated
Material Type	Steel

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +85 °C (-40 °F to +185 °F)

FL2-96SPNL2

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

