

FDF-ACCSPLCE



FDF Fiber Splice Panel, 8 drawers for 192 splices, unloaded, 8 in x 23 in, putty white

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber splice panel
Product Series	FDF

General Specifications

Functionality	Splicing
Application	Used in rear-load FDF-style frames only
Body Style	Symmetrical
Color	Putty white
Color, front	Putty white
Growth Configuration	Unloaded
Interface, front	Unloaded
Patch Cord Entry Location	Front, left side Front, right side
Patching Capacity, maximum	0
Rack Type	EIA 23 in
Rack Units	4.6
Shelf Movement	Fixed
Splicing Capacity, maximum	192

Dimensions

Height	203.2 mm 8 in
Width	584.2 mm 23 in
Depth	304.8 mm 12 in

Material Specifications

FDF-ACCSPLCE

Finish	Powder coated
Material Type	Steel

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
------------------------------	--------------------------------------

Packaging and Weights

Included	Mounting hardware
Packaging quantity	1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

