HELIAX® Remote Radio Head Power Cable, 2 conductors with shield, 6 = AWG, one red conductor and one black conductor

Product Classification

Regional Availability North America

Product Type Power cable assembly

 Product Brand
 HELIAX®

 Product Series
 DPJ

Ordering Note ANDREW® non-standard product

General Specifications

 Cable Type
 Power

 Conductor Type, singles
 Stranded

Conductors, quantity 2

Construction Type Non-armored

Jacket Color Black

Jacket Color, singles

Black | Red

Supported Application

Industrial

Dimensions

Diameter Over Conductor, singles, specific0.1260 in per 105 strandsDiameter Over Dielectric4.724 mm | 0.186 inDiameter Over Jacket, nominal16.281 mm | 0.641 inJacket Thickness1.143 mm | 0.045 in

Conductor Gauge, singles 6 AWG

Electrical Specifications

Conductor dc Resistance 3.478 ohms/km | 1.06 ohms/kft

Conductor dc Resistance Note Maximum value based on a standard condition of 20 °C (68 °F)

Safety Voltage Rating 600 V



DPJ-206

Material Specifications

Conductor Material Tinned copper

Dielectric Material PVC

Drain Wire MaterialTinned copperFiller MaterialPolypropylene

Insulation Material, singles PVC

Jacket Material PVC

Outer Shield (Braid) Coverage 65 %

Outer Shield (Braid) Material Tinned copper

Outer Shield (Tape) Material Aluminum/Poly, non-bonded

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+90 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+194 \,^{\circ}\text{F}$)

Environmental Space UV resistant for outdoor and/or direct burial installations

Safety Standard NEC Article 336 (Type TC)

