

CCASD | IP6A-12LUTP-01S-1LK12

Base Product



InstaPATCH® Cu GigaSPEED X10D® U/UTP LSZH Preterminated Copper Cable, single row standard density outlet to dual row OneLink 2x6, 12 links

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Copper trunk cable assembly
Product Brand	GigaSPEED X10D® InstaPATCH® Cu

General Specifications

ANSI/TIA Category	6A
Cable Type	U/UTP (unshielded)
Conductor Type	Solid
Interface, Connector A	Information outlet
Interface Feature, connector A	Single row Standard density
Interface, Connector B	OneLink 2x6
Interface Feature, connector B	Standard
Link Count	12
Wiring	T568B

Dimensions

Cable Assembly Length Range (m)	2 – 30
Cable Assembly Length Range (ft)	7 – 98

Electrical Specifications

dc Resistance, maximum	0.3 ohm
Safety Voltage Rating	300 V

Ordering Tree

CCASD | IP6A-12LUTP-01S-1LK12

	1	2	3	4	5	6	7	8	9	10	11	12				
	C	A	A	A	C	-	1	1	H	A	B	B	F	0	5	0

Cable Type	Connector B	Orientation A	Orientation B
1 A Cat 6A X10D – U/UTP (Plenum) B Cat 6A X10D – U/UTP (Riser) C Cat 6A X10D – U/UTP (LSZH) D Cat 6A X10D – F/UTP (Plenum) E Cat 6A X10D – F/UTP (Riser) F Cat 6A X10D – F/UTP (LSZH) G Cat 6 XL – U/UTP (Plenum) H Cat 6 XL – U/UTP (Riser) J Cat 6 XL – U/UTP (LSZH) Q Cat 6A X10D – S/FTP (LSZH) R Cat 6 – U/UTP Class B Rated (LSZH) S Cat 6A – U/UTP Class B Rated (LSZH) Y Cat 6A X10D SD – U/UTP (Riser)	3 A Outlet* – Single Row Standard Density B Outlet* – Dual Row Standard Density C Outlet* – Dual Row High Density G RJ45 Plug* – Single Row Standard Density H RJ45 Plug* – Dual Row Standard Density J RJ45 Plug* – Dual Row High Density N 1100 Module R 360 1100 Evolve Module S OneLink 2x6 T OneLink 2x4	5 1 Trident Series Flat 2 Right Paired Flat 3 Right Series Flat 4 Left Paired Flat 5 Left Series Flat 6 Trident Paired Flat A Trident Series Angled B Right Paired Angled C Right Series Angled D Left Paired Angled E Left Series Angled F Trident Paired Angled	6 1 Trident Series Flat 2 Right Paired Flat 3 Right Series Flat 4 Left Paired Flat 5 Left Series Flat 6 Trident Paired Flat A Trident Series Angled B Right Paired Angled C Right Series Angled D Left Paired Angled E Left Series Angled F Trident Paired Angled X Not Applicable

Connector A	Link	Outlet Color	UOM	Length
2 A Outlet* – Single Row Standard Density B Outlet* – Dual Row Standard Density C Outlet* – Dual Row High Density G RJ45 Plug* – Single Row Standard Density H RJ45 Plug* – Dual Row Standard Density J RJ45 Plug* – Dual Row High Density N 1100 Module R 360 1100 Evolve Module S OneLink 2x6 T OneLink 2x4 X Unterminated	4 B 6 C 8 D 12 E 16 F 18 G 24	9 0 Not Applicable 1 Black (BK) 2 Blue (BL) 3 White (WH)	11 F Foot M Meter	12 XXX

Bundling	Jacket Color	Labeling
7 H Hook-n-loop S Sleaving	10 B White (WH) C Slate (SL) Z Blue (BL)	8 A Generic Label

- Cords > 1m are authorized for use in channels and are an effective standalone method used to connect active devices
- Cords < 1m are also valid elements for use in a channel or as an equipment interconnect, but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Environmental Space	Low Smoke Zero Halogen (LSZH)
Flammability Rating	UL 94 V-0

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

Included Products

- 3095B-4/24 – GigaSPEED X10D® 3095B Category 6A U/UTP Cable, non-plenum, 4 pair count
- MGS600 – GigaSPEED X10D® M-Series Modular Jack, RJ45, Cat6A Unshielded