# UGVQPQXQH

#### **Base Product**



Ultra Low Loss (ULL) OM5 MPO QSFP (Unpinned) to MPO QSFP (Pinned), Pre-terminated Trunk Cable, MPO8, 48-Fiber, Plenum

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | Europe | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

**Product Type** Fiber trunk cable assembly

Product Brand SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

# General Specifications

Color, boot A Gray

Color, connector A Lime green

Color, boot B Gray

Color, connector BLime greenConstruction TypeStrandedFurcation ColorLime green

Interface, Connector AMPO-08/UPC FemaleInterface Feature, connector AQSFP configuration

Interface, Connector B MPO-08/UPC Male

Interface Feature, connector B QSFP configuration

**Jacket Color** Lime green

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 8

Total Fibers, quantity 48

Dimensions

Breakout Length 33 in


Page 1 of 10

# UGVQPQXQH

Cable Assembly Length Range (m) 3 - 999

Cable Assembly Length Range (ft) 10 - 999

# Ordering Tree



## Mechanical Specifications

Cable Retention Strength, maximum  $11.24 \text{ lb} @ 0 \degree | 4.40 \text{ lb} @ 90 \degree$ 

Optical Specifications

**Fiber Mode** Multimode

**Fiber Type** OM5, LazrSPEED®

# **Environmental Specifications**

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Plenum

# Regulatory Compliance/Certifications

# Agency Classification ANATEL Compliant

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



### Included Products

760223008 – Fiber indoor cable, LazrSPEED® Plenum MPO Trunk, 72 fiber multi-unit with 12 fiber subunits, P-072-MP-5G-F12LM Multimode OM5, Gel-free, Feet jacket marking, Lime green jacket color

Page 2 of 10



# UGVQPQXQH

860633311 – MPO8, ULTRA LOW LOSS, FEMALE, OM5, LIME, 3mm

860633312 – MPO8, ULTRA LOW LOSS, MALE, OM5, LIME, 3mm

# 760223008 | P-072-MP-5G-F12LM



Fiber indoor cable, LazrSPEED® Plenum MPO Trunk, 72 fiber multi-unit with 12 fiber subunits, Multimode OM5, Gel-free, Feet jacket marking, Lime green jacket color

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

Product Type Fiber indoor cable

**Product Series** P-MP

General Specifications

Cable Type MPO trunk cable

Construction Type Non-armored

Subunit Type Gel-free

Jacket Color Lime green

Jacket Marking Feet

Subunit, quantity 6

Fibers per Subunit, quantity 12

Total Fiber Count 72

**Dimensions** 


**Buffer Tube/Subunit Diameter** 3 mm | 0.118 in

**Diameter Over Jacket** 10.7 mm | 0.421 in

Representative Image



# 760223008 | P-072-MP-5G-F12LM



# Mechanical Specifications

Minimum Bend Radius, loaded161 mm6.339 inMinimum Bend Radius, unloaded107 mm4.213 in

Tensile Load, long term, maximum 400 N | 89.924 lbf

Tensile Load, short term, maximum 1335 N | 300.12 lbf

**Compression** 10 N/mm | 57.101 lb/in

**Compression Test Method** FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 0.74 N-m | 6.55 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

**Vertical Rise, maximum** 368 m | 1,207.349 ft

**Optical Specifications** 

Fiber Type OM5, LazrSPEED® wideband | OM5, LazrSPEED® wideband

# **Environmental Specifications**

Installation temperature  $0 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C (+32 °F to} + 158 \,^{\circ}\text{F)}$ Operating Temperature  $0 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C (+32 °F to} + 158 \,^{\circ}\text{F)}$ 

Page 5 of 10



# 760223008 | P-072-MP-5G-F12LM

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  ( $-40 \,^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

Environmental Space Plenum

Flame Test Listing NEC OFNP (ETL) and c(ETL)

Flame Test Method NFPA 130 | NFPA 262

**Environmental Test Specifications** 

**Heat Age** 0 °C to +85 °C (+32 °F to +185 °F)

**Heat Age Test Method** IEC 60794-1 F9

**Low High Bend** 0 °C to +70 °C (+32 °F to +158 °F)

**Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11

**Temperature Cycle**  $0 \,^{\circ}\text{C to } +70 \,^{\circ}\text{C (+32 °F to } +158 \,^{\circ}\text{F)}$ 

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

**Cable weight** 111 kg/km | 74.589 lb/kft

# Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



#### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable





### MPO8, ULTRA LOW LOSS, FEMALE, OM5, LIME, 3mm

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

 Portfolio
 CommScope®

 Product Type
 Fiber connector

 Product Brand
 LazrSPEED®

General Specifications

**Color** Lime green

Color, boot Gray
Ferrule Geometry Flat

Interface MPO/UPC Female

Interface Feature Unpinned

**Total Fiber Count** 8

**Dimensions** 

**Length** 60.1 mm | 2.366 in

**Compatible Cable Diameter** 3 mm | 0.118 in

Material Specifications

Ferrule Material Polymer

Mechanical Specifications

Cable Retention Strength, maximum  $11.24 \text{ lb} @ 0 ^{\circ}$ 

**Optical Specifications** 

**Fiber Mode** Multimode

**Fiber Type** OM5, LazrSPEED® wideband

**Insertion Loss Change, mating** 0.3 dB

Optical Components Standard ANSI/TIA-568-C.3

**COMMSCOPE®** 

# 860633311

Insertion Loss Change, temperature0.3 dBInsertion Loss, maximum0.2 dBReturn Loss, minimum27 dB

# Packaging and Weights

Packaging quantity 1

## Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



#### \* Footnotes

**Insertion Loss Change, mating**TIA-568: Maximum insertion loss change after 500 matings

 $\textbf{Insertion Loss Change, temperature} \quad \text{Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)}$ 





### MPO8, ULTRA LOW LOSS, MALE, OM5, LIME, 3mm

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

 Portfolio
 CommScope®

 Product Type
 Fiber connector

 Product Brand
 LazrSPEED®

General Specifications

**Color** Lime green

Color, boot Gray
Ferrule Geometry Flat

Interface MPO/UPC Male

Interface FeaturePinnedTotal Fiber Count8

Dimensions

**Length** 60.1 mm | 2.366 in

**Compatible Cable Diameter** 3 mm | 0.118 in

Material Specifications

Ferrule Material Polymer

Mechanical Specifications

Cable Retention Strength, maximum  $11.24 \text{ lb} @ 0 ^{\circ}$ 

**Optical Specifications** 

**Fiber Mode** Multimode

**Fiber Type** OM5, LazrSPEED® wideband

**Insertion Loss Change, mating** 0.3 dB

Optical Components Standard ANSI/TIA-568-C.3

Page 9 of 10

# 860633312

Insertion Loss Change, temperature0.3 dBInsertion Loss, maximum0.2 dBReturn Loss, minimum27 dB

# Packaging and Weights

Packaging quantity 1

## Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



### \* Footnotes

**Insertion Loss Change, mating** TIA-568: Maximum insertion loss change after 500 matings

**Insertion Loss Change, temperature** Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)

