

# L4P43A-PNMNR-2M

---

LDF4-50A SureFlex® Jumper with interface types 7-16 N Male and 7-16 N Male Right angle, 2 m



## Product Classification

|                       |                                      |
|-----------------------|--------------------------------------|
| <b>Product Type</b>   | Wireless transmission cable assembly |
| <b>Product Series</b> | LDF4-50A                             |

## General Specifications

|                                |                  |
|--------------------------------|------------------|
| <b>Attachment, Connector B</b> | Field attachment |
| <b>Body Style, Connector A</b> | Straight         |
| <b>Body Style, Connector B</b> | Right angle      |
| <b>Interface, Connector A</b>  | N Male           |
| <b>Interface, Connector B</b>  | N Male           |

## Dimensions

|                     |                |
|---------------------|----------------|
| <b>Length</b>       | 2 m   6.562 ft |
| <b>Nominal Size</b> | 1/2 in         |

## VSWR/Return Loss

| Frequency Band | VSWR | Return Loss (dB) |
|----------------|------|------------------|
| 710–806 MHz    | 1.2  | 20.83            |
| 806–960 MHz    | 1.15 | 23.13            |
| 1700–2180 MHz  | 1.15 | 23.13            |
| 2535–2655 MHz  | 1.2  | 20.83            |

## Jumper Assembly Sample Label

# L4P43A-PNMNR-2M



## Environmental Specifications

**Immersion Test Method** Meets IEC 60529:2001, IP68 in mated condition

## Regulatory Compliance/Certifications

**Agency** ISO 9001:2015  
**Classification** Designed, manufactured and/or distributed under this quality management system



## Included Products

- LDF4-50A — LDF4-50A, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket (Halogen free jacketing non-fire-retardant)