

# F1A-PDRDR-30N

---

FSJ1-50A SureFlex® Jumper with interface types 7-16 DIN Male Right Angle and 7-16 DIN Male Right Angle, 0.76 m



## Product Classification

**Product Type** SureFlex® standard

**Product Series** FSJ1-50A

## General Specifications

**Body Style, Connector A** Right angle

**Body Style, Connector B** Right angle

**Interface, Connector A** 7-16 DIN Male

**Interface, Connector B** 7-16 DIN Male

**Orientation** 0°

**Specification Sheet Revision Level** A

## Dimensions

**Length** 0.76 m | 2.493 ft

**Nominal Size** 1/4 in

## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.33	17

## Jumper Assembly Sample Label

# F1A-PDRDR-30N



## Environmental Specifications

### Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

## Regulatory Compliance/Certifications

### Agency

ISO 9001:2015

### Classification

Designed, manufactured and/or distributed under this quality management system



## Included Products

- |            |   |  |
|------------|---|--|
| 35422-33   | - | Heat Treated FSJ1-50A, HELIAX® Superflexible Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE Jacket  |
| 35422-75   | - | Heat Treated FSJ1RK-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/4 in, black non-halogenated, fire retardant polyolefin jacket            |
| FSJ1-50A   | - | FSJ1-50A, HELIAX® Superflexible Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE jacket   |
| FSJ1RK-50A | - | FSJ1-50A, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/4 in, black non-halogenated, fire retardant polyolefin jacket, B2ca s1a d0 a1 Compliant |