760133546



RBA84-36 24V-Primary / 48V-Secondary Power & Battery Cabinet

- Sealed to outside environment
- Double wall construction

OBSOLETE

Product Classification	
Product Type	Power supply enclosure
General Specifications	
Access	Front door Rear door
Batteries	Not included
Batteries Supported	180 A-h batteries
Cabinet Type	Battery back-up cabinet
Color	Beige
Cooling	Heat exchange
Dimensions	
Height	2,133.6 mm 84 in
Width	914.4 mm 36 in
Depth	990.6 mm 39 in
Electrical Specifications	
Battery String Current, maximum	4320 A-h @ 24 Vdc
Voltage	24 Vdc 48 Vdc
Material Specifications	
Finish	Powder coated

Environmental Specifications

Qualification Standards

OSHA | Telcordia GR-487

Page 1 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: September 12, 2023



760133546

Packaging and Weights

 Weight, net
 371.946 kg | 820 lb

Weight, with batteries, typical

1,995.806 kg | 4400 lb

Regulatory Compliance/Certifications

Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system



Agency

Page 2 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: September 12, 2023

