

CS44Z3 ETL Verified Category 6A U/UTP LSZH Cable, white jacket, 4 pair count, 3280 ft (1000 m) length, reel

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America

Portfolio NETCONNECT®

Product Type Twisted pair cable

General Specifications

Product Number CS44Z3

ANSI/TIA Category 6A

Cable Component Type Horizontal

Cable Type U/UTP (unshielded)

Conductor Type, singlesSolidConductors, quantity8Jacket ColorWhitePairs, quantity4

Separator Type Isolator

Transmission Standards ANSI/TIA-568.2-D | ISO/IEC 11801 Class EA

**Dimensions** 

 Cable Length
 1,000 m | 3,280.84 ft

 Diameter Over Insulated Conductor
 0.864 mm | 0.034 in


 Diameter Over Jacket, nominal
 7.239 mm | 0.285 in

 Jacket Thickness
 1.295 mm | 0.051 in

Conductor Gauge, singles 23 AWG

Cross Section Drawing





### **Electrical Specifications**

dc Resistance Unbalance, maximum 4 %

dc Resistance, maximum 7.61 ohms/100 m | 2.32 ohms/100 ft

Mutual Capacitance at Frequency 6.0 nF/100 m @ 1 kHz

Nominal Velocity of Propagation (NVP) 66 %

**Operating Frequency, maximum** 550 MHz

Operating Voltage, maximum 80 V

**Remote Powering**Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according

to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA

TSB-184-A

С

Safety Voltage Rating 300 V

Segregation Class



#### Electrical Cable Performance

**CS** CommScope

STD Refers to the standard value listed under Transmission Standards in the Electrical Specifications above

TYP Typical Electrical Performance

IL Insertion Loss (dB/100m) NEXT Near End Crosstalk (dB/100m)

 ACR
 Attenuation to Crosstalk Ratio (dB/100m)
 PSNEXT
 Power Sum Near End Crosstalk (db/100m)

 PSACR
 Power Sum Attenuation to Crosstalk Ratio (dB/100m)
 ACRF
 Attenuation to Crosstalk Ratio - Far End (dB/100m)

PSACRF Power Sum Attenuation to Crosstalk Ratio - Far End (dB/100m) RL Return Loss (dB)

TCL Transverse Conversion Loss (dB/100m) ELTCTL Equal Level Transverse Conversion Transfer Loss (dB/100m)

Freq. MHz	IL		NEXT		ACR		PSNEXT		PSACR		ACRF		PSACRF		RL	
	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP
1	2.1	1.8	74.3	90.6	72.2	88.8	72.3	88.3	70.2	86.5	67.8	82.1	64.8	80.3	20	32.2
4	3.8	3.6	65.3	82.4	61.5	78.8	63.3	80.2	59.5	76.6	55.8	70.1	52.8	68.4	23	33.9
8	5.3	5.1	60.8	77.6	55.4	72.5	58.8	75.8	53.4	70.7	49.7	64.1	46.7	62.3	24.5	36.7
10	5.9	5.7	59.3	76.4	53.4	70.7	57.3	74.4	51.4	68.7	47.8	62.2	44.8	60.4	25	37.7
16	7.5	7.3	56.2	73.1	48.8	65.9	54.2	71.3	46.8	64	43.7	58.2	40.7	56.4	25	38.7
20	8.4	8.1	54.8	71.5	46.4	63.4	52.8	69.7	44.4	61.6	41.8	56.4	38.8	54.5	25	38.7
25	9.4	9.1	53.3	70.2	44	61.1	51.3	68.3	42	59.2	39.8	54.5	36.8	52.6	24.3	35.5
31.25	10.5	10.2	51.9	68.6	41.4	58.4	49.9	66.7	39.4	56.5	37.9	52.7	34.9	50.7	23.6	37.2
62.5	15	14.6	47.4	64.2	32.4	49.6	45.4	62.3	30.4	47.7	31.9	46.6	28.9	44.7	21.5	34.6
100	19.1	18.6	44.3	60.8	25.2	42.1	42.3	59	23.2	40.3	27.8	42.5	24.8	40.5	20.1	30.3
155	24.1	23.4	41.4	58.4	17.4	35	39.4	56.4	15.4	33	24	38.9	21	37	18.8	30.8
200	27.6	26.8	39.8	56	12.2	29.2	37.8	54.2	10.2	27.4	21.8	36.6	18.8	34.6	18	30
250	31.1	30.1	38.3	54.3	7.3	24.2	36.3	52.5	5.3	22.3	19.8	34.6	16.8	32.6	17.3	30.5
300	34.3	33.1	37.1	53.1	2.9	19.9	35.1	51.2	0.9	18.1	18.3	33.1	15.3	31.2	16.8	31.1
350	37.2	36	36.1	51.8	-1.1	15.8	34.1	49.9	-3.1	13.9	16.9	31.9	13.9	29.9	16.3	31.7
400	40.1	38.8	35.3	50.8	-4.8	12	33.3	48.8	-6.8	10	15.8	30.6	12.8	28.6	15.9	31.5
500	45.3	43.6	33.8	47.9	-11.4	4.3	31.8	45.8	-13.4	2.2	13.8	28.7	10.8	26.7	15.2	32
550		43.8		48		4.1		45.9		2		28.6		26.7		31.9
650		50.2		43.5		-6.7		41.5		-8.8		25.7		23.5		25.3

### Material Specifications

Conductor Material Bare copper

**Insulation Material** Polyolefin

Jacket Material Low Smoke Zero Halogen (LSZH)

Separator MaterialPolyolefinSeparator 2 MaterialPolyolefin

Mechanical Specifications

**Pulling Tension, maximum** 11.34 kg | 25 lb



### **Environmental Specifications**

Installation temperature 0 °C to +60 °C (+32 °F to +140 °F)

**Operating Temperature**  $-20 \, ^{\circ}\text{C} \text{ to } +60 \, ^{\circ}\text{C} \text{ (-4 } ^{\circ}\text{F to } +140 \, ^{\circ}\text{F)}$ 

Acid Gas Test Method IEC 60754-2

EN50575 CPR Cable EuroClass Fire PerformanceDcaEN50575 CPR Cable EuroClass Smoke Ratings2EN50575 CPR Cable EuroClass Droplets Ratingd2EN50575 CPR Cable EuroClass Acidity Ratinga1

Environmental Space Low Smoke Zero Halogen (LSZH)

Flame Test Method IEC 60332-3-22

Smoke Test Method IEC 61034-2

Packaging and Weights

**Cable weight** 54.913 kg/km | 36.9 lb/kft

Packaging Type Reel

### Regulatory Compliance/Certifications

#### Agency Classification

CENELEC EN 50575 compliant, Declaration of Performance (DoP) available

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

CENELEC

