

CS37P ETL Verified Category 6 U/UTP Cable, plenum, gray jacket, 4 pair count, 3000 ft (914 m) length reel



Product Classification

Regional Availability	North America
Portfolio	Uniprise®
Product Type	Twisted pair cable


General Specifications

Product Number	CS37P
ANSI/TIA Category	6
Cable Component Type	Horizontal
Cable Type	U/UTP (unshielded)
Conductor Type, singles	Solid
Conductors, quantity	8
Jacket Color	Gray
Note	All electrical transmission tests include swept frequency measurements
Pairs, quantity	4
Separator Type	Isolator
Transmission Standards	ANSI/TIA-568.2-D CENELEC EN 50288-6-1 ISO/IEC 11801 Class E

Dimensions

Cable Length	3000 ft 914.4 m
Cable Length Tolerance	±5%
Diameter Over Insulated Conductor	0.038 in 0.978 mm
Diameter Over Jacket, nominal	0.222 in 5.639 mm
Jacket Thickness	0.019 in 0.483 mm
Conductor Gauge, singles	23 AWG

Cross Section Drawing



Electrical Specifications

Characteristic Impedance	100 ohm
dc Resistance Unbalance, maximum	5 %
dc Resistance, maximum	8 ohms/100 m 2.438 ohms/100 ft
Delay Skew, maximum	45 ns
Dielectric Strength, minimum	1500 Vac 2500 Vdc
Mutual Capacitance at Frequency	5.6 nF/100 m @ 1 kHz
Nominal Velocity of Propagation (NVP)	75 %
Operating Frequency, maximum	400 MHz
Operating Voltage, maximum	80 V
Remote Powering	Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A
Safety Voltage Rating	300 V

Electrical Cable Performance

CS	CommScope	NEXT	Near End Crosstalk (dB/100m)
STD	Refers to the standard value listed under Transmission Standards in the Electrical Specifications above	PSNEXT	Power Sum Near End Crosstalk (db/100m)
TYP	Typical Electrical Performance	ACRF	Attenuation to Crosstalk Ratio - Far End (dB/100m)
IL	Insertion Loss (dB/100m)	RL	Return Loss (dB)
ACR	Attenuation to Crosstalk Ratio (dB/100m)	ELTCTL	Equal Level Transverse Conversion Transfer Loss (dB/100m)
PSACR	Power Sum Attenuation to Crosstalk Ratio (dB/100m)		
PSACRF	Power Sum Attenuation to Crosstalk Ratio - Far End (dB/100m)		
TCL	Transverse Conversion Loss (dB/100m)		

Freq. MHz	IL			NEXT			ACR			PSNEXT			PSACR			ACRF			PSACRF			RL		
	CS	STD	TYP	CS	STD	TYP	CS	STD	TYP	CS	STD	TYP	CS	STD	TYP	CS	STD	TYP	CS	STD	TYP	CS	STD	TYP
1	2	2	1.8	77.3	74.3	90.3	75.3	72.3	88.5	75.3	72.3	88.1	73.3	70.3	86.3	68.8	67.8	84.1	65.8	64.8	82.6	20	20	32
4	3.8	3.8	3.6	68.3	65.3	82.7	64.5	61.5	79.1	66.3	63.3	80.4	62.5	59.5	76.8	56.8	55.8	72.7	53.8	52.8	71.4	23.6	23	30
8	5.3	5.3	5.1	63.8	60.8	78.1	58.5	55.4	72.9	61.8	58.8	75.8	56.5	53.4	70.6	50.7	49.7	66.9	47.7	46.7	65.5	25.4	24.5	34.3
10	5.9	6	5.8	62.3	59.3	76.5	56.4	53.3	70.7	60.3	57.3	74.3	54.4	51.3	68.5	48.8	47.8	65	45.8	44.8	63.6	26	25	34.9
16	7.5	7.6	7.3	59.2	56.2	73.5	51.7	48.7	66.1	57.2	54.2	71.3	49.7	46.7	64	44.7	43.7	61	41.7	40.7	59.5	26	25	35.2
20	8.4	8.5	8.2	57.8	54.8	72	49.4	46.3	63.8	55.8	52.8	69.8	47.4	44.3	61.6	42.8	41.8	59	39.8	38.8	57.6	26	25	35
25	9.4	9.5	9.2	56.3	53.3	70.3	46.9	43.8	61	54.3	51.3	68.2	44.9	41.8	58.9	40.8	39.8	57.1	37.8	36.8	55.7	25.3	24.3	36.1
31.25	10.6	10.7	10.3	54.9	51.9	68.9	44.3	41.2	58.6	52.9	49.9	66.8	42.3	39.2	56.5	38.9	37.9	55.2	35.9	34.9	53.8	24.6	23.6	36.4
62.5	15.3	15.4	14.8	50.4	47.4	63.8	35.1	32	49	48.4	45.4	61.7	33.1	30	46.8	32.9	31.9	49	29.9	28.9	47.6	22.5	21.5	34.1
100	19.7	19.8	19	47.3	44.3	60.5	27.6	24.5	41.6	45.3	42.3	58.3	25.6	22.5	39.3	28.8	27.8	44.7	25.8	24.8	43.3	21.1	20.1	32.4
155	25	25.2	23.9	44.4	41.4	58.6	19.5	16.3	34.7	42.4	39.4	56.3	17.5	14.3	32.4	25	24	41.3	22	21	39.8	19.8	18.8	30
200	28.8	29	27.4	42.8	39.8	55.4	14	10.8	28	40.8	37.8	53.3	12	8.8	26	22.8	21.8	38.5	19.8	18.8	37.1	19	18	29.3
250	32.6	32.8	30.8	41.3	38.3	54	8.7	5.5	23.2	39.3	36.3	51.9	6.7	3.5	21	20.8	19.8	36.5	17.8	16.8	35	18.3	17.3	28.3
300	36.2		34	40.1		52.2	4		18.2	38.1		50.2	2		16.2	19.3		34.6	16.3		33.1	17.8		28.2
350	39.5		37	39.1		50.9	-0.4		14	37.1		48.9	-2.4		12	17.9		33	14.9		31.4	17.3		28.1
400	42.7		39.7	38.3		49.9	-4.4		10.2	36.3		47.9	-6.4		8.2	16.8		30.9	13.8		29.4	16.9		28.6
500			45.2			47.5			2.3			45.5			0.3			26.9			25.2			28.5
550			44.9			50.9			6			48.8			3.9			28.7			27.3			33.6
650			49.8			46.4			-2.5			44.2			-5.6			23.3			21.5			25.3

Material Specifications

Conductor Material	Bare copper
Insulation Material	FEP Polyolefin
Jacket Material	PVC
Separator Material	FEP

Mechanical Specifications

Pulling Tension, maximum	25 lb 11.34 kg
---------------------------------	------------------

Environmental Specifications

UN874026784/30 | CS37P GRY C6 4/23 U/UTP RL 3KFT

Installation temperature	0 °C to +60 °C (+32 °F to +140 °F)
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Environmental Space	Plenum
Temperature Rating, ETL	75 °C 167 °F
Flame Test Method	CMP/FT6 NEC Article 800 NFPA 262 UL 444 UL 910
Smoke Test Method	CMP/FT6

Packaging and Weights

Cable weight	27.88 lb/kft 41.49 kg/km
Packaging Type	Reel

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

