

HHT4-65B-R2

12-port, Dual Band, DualPol® Planar Array® Antenna, 4x 1850–1995 and 8x 2490–2690MHz, 65° HPBW, 2x internal RET.



- 2 columns for 1895 MHz and 4 columns for 2490-2690 MHz
- Two internal RETs to control the antenna arrays
- Integrated with a calibration board

OBSOLETE

This product was discontinued on: **March 31, 2021**

General Specifications

| | |
|---|--|
| Antenna Type | Sector |
| Band | Multiband |
| Calibration Connector Interface | N Female |
| Calibration Connector Quantity | 1 |
| Color | Light Gray (RAL 7035) |
| Grounding Type | RF connector inner conductor and body grounded to reflector and mounting bracket |
| Performance Note | Outdoor usage |
| Radome Material | PVC, UV resistant |
| Radiator Material | Brass Low loss circuit board |
| Reflector Material | Aluminum |
| RF Connector Interface | 4.1-9.5 DIN Female |
| RF Connector Location | Bottom |
| RF Connector Quantity, high band | 12 |
| RF Connector Quantity, total | 12 |

Remote Electrical Tilt (RET) Information

| | |
|--------------------------------|---------------|
| RET Interface, quantity | 2 male |
| Input Voltage | 10–30 Vdc |
| Internal RET | High band (2) |


HHT4-65B-R2

| | |
|--|----------------------------|
| Power Consumption, idle state, maximum | 1 W |
| Power Consumption, normal conditions, maximum | 13 W |
| Protocol | 3GPP/AISG 2.0 (Single RET) |

Dimensions

| | |
|---|---------------------|
| Width | 320 mm 12.598 in |
| Depth | 170 mm 6.693 in |
| Length | 1820 mm 71.654 in |
| Net Weight, without mounting kit | 24 kg 52.911 lb |
| TDD Column Spacing | 75 mm 2.953 in |

Port Configuration



Electrical Specifications

| | |
|---------------------------------|-----------------------------------|
| Impedance | 50 ohm |
| Operating Frequency Band | 1850 – 1995 MHz 2490 – 2690 MHz |
| Polarization | ±45° |

Beam Forming Weights

HHT4-65B-R2

| | | Prefered New wt/phase table | | | | | | | | |
|-------------|-------------------------------------|-----------------------------|-------|-------|-------|-------|-------|-------|-------|-------|
| HHT4-65B-R2 | | | Port1 | Port2 | Port3 | Port4 | Port5 | Port6 | Port7 | Port8 |
| P0 | Broadcast_65° for tilt 0-3 | Amp(voltage) | 0.81 | 0 | 1 | 0 | 0.73 | 0 | 0.6 | 0 |
| | | Phz | 0 | 0 | 115 | 0 | 100 | 0 | 0 | 0 |
| P1 | Broadcast_65° for tilt 0-3 | Amp(voltage) | 0 | 0.81 | 0 | 1 | 0 | 0.73 | 0 | 0.6 |
| | | Phz | 0 | 0 | 0 | 115 | 0 | 100 | 0 | 0 |
| P0 | Broadcast_65° for tilt 4-8 | Amp(voltage) | 0.81 | 0 | 1 | 0 | 0.73 | 0 | 0.6 | 0 |
| | | Phz | 0 | 0 | 130 | 0 | 100 | 0 | 7 | 0 |
| P1 | Broadcast_65° for tilt 4-8 | Amp(voltage) | 0 | 0.81 | 0 | 1 | 0 | 0.73 | 0 | 0.6 |
| | | Phz | 0 | 0 | 0 | 130 | 0 | 100 | 0 | 7 |
| P0 | FullPower_Boardcast_65° for tilt0-8 | Amp(voltage) | 1 | 1 | 1 | 1 | 0 | 0 | 0 | 0 |
| | | Phz | 80 | 57 | 0 | 137 | 0 | 0 | 0 | 0 |
| P1 | FullPower_Boardcast_65° for tilt0-8 | Amp(voltage) | 0 | 0 | 0 | 0 | 1 | 1 | 1 | 1 |
| | | Phz | 0 | 0 | 0 | 0 | 93 | -123 | 0 | -30 |
| +45 | Service Beam_0° for tilt0-8 | Amp(voltage) | 1 | 0 | 1 | 0 | 1 | 0 | 1 | 0 |
| | | Phz | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |
| -45 | Service Beam_0° for tilt0-8 | Amp(voltage) | 0 | 1 | 0 | 1 | 0 | 1 | 0 | 1 |
| | | Phz | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |
| +45 | Service Beam_30° for tilt0-8 | Amp(voltage) | 1 | 0 | 1 | 0 | 1 | 0 | 1 | 0 |
| | | Phz | 0 | 0 | 120 | 0 | -120 | 0 | 0 | 0 |
| -45 | Service Beam_30° for tilt0-8 | Amp(voltage) | 0 | 1 | 0 | 1 | 0 | 1 | 0 | 1 |
| | | Phz | 0 | 0 | 0 | 120 | 0 | -120 | 0 | 0 |
| +45 | Service Beam_-30° for tilt0-8 | Amp(voltage) | 1 | 0 | 1 | 0 | 1 | 0 | 1 | 0 |
| | | Phz | 0 | 0 | -120 | 0 | 120 | 0 | 0 | 0 |
| -45 | Service Beam_-30° for tilt0-8 | Amp(voltage) | 0 | 1 | 0 | 1 | 0 | 1 | 0 | 1 |
| | | Phz | 0 | 0 | 0 | -120 | 0 | 120 | 0 | 0 |

Electrical Specifications

| | | |
|---|------------------|------------------|
| Frequency Band, MHz | 1850–1995 | 2490–2690 |
| Beam Tilt, degrees | 0–8 | 0–8 |
| Beam Tilt Tolerance, degrees | ±1 | ±1 |
| Coupling level, Amp, Antenna port to Cal port, dB | | 26 |
| Coupling level, max Amp Δ, Antenna port to Cal port, dB | | ±2 |
| Coupler, max Amp Δ, Antenna port to Cal port, dB | | 0.9 |
| Coupler, max Phase Δ, Antenna port to Cal port, degrees | | 7 |
| Isolation, Cross Polarization, dB | 25 | 25 |
| Isolation, Cross Polarization, port to port, dB | 25 | 25 |
| Isolation, Cross Polarization, port to port, between two columns, dB | 25 | 25 |
| VSWR Return loss, dB | 1.5 14.0 | 1.5 14.0 |
| PIM, 3rd Order, 2 x 20 W, dBc | -153 | -146 |

Electrical Specifications, Broadcast 65°

| | |
|---|------------------|
| Frequency Band, MHz | 2490–2690 |
| Gain, dBi | 17 |
| Beamwidth, Horizontal, degrees | 65 |
| Beamwidth, Horizontal Tolerance, degrees | ±5 |
| Beamwidth, Vertical, degrees | 5 |
| Beamwidth, Vertical Tolerance, degrees | ±0.5 |

HHT4-65B-R2

| | |
|---|-----|
| CPR at Boresight, dB | 17 |
| Front-to-Back Total Power at 180° ± 30°, dB | 27 |
| Null Fill, dB | -22 |
| USLS (First Lobe), dB | 18 |

Electrical Specifications, Service Beam

| | |
|---|------------------|
| Frequency Band, MHz | 2490–2690 |
| Steered 0° Gain, dBi | 22.5 |
| Steered 0° Gain Tolerance, dBi | ±0.5 |
| Steered 0° Beamwidth, Horizontal, degrees | 22 |
| Steered 0° CPR at Beampeak, dB | 18 |
| Steered 0° Front-to-Back Total Power at 180° ± 30°, dB | 30 |
| Steered 0° Horizontal Sidelobe, dB | -10 |
| Steered 13° USLS (First Lobe), dB | 5 |
| Steered 30° Gain, dBi | 21 |
| Steered 30° Gain Tolerance, dBi | ±0.5 |
| Steered 42° Front-to-Back Total Power at 180° ± 30°, dB | 5 |

Electrical Specifications, Single Column

| Frequency Band, MHz | 1850–1995 | 2490–2690 |
|---|------------------|------------------|
| Gain, dBi | 17.4 | 17.6 |
| Beamwidth, Horizontal, degrees | 64 | 70 |
| Beamwidth, Horizontal Tolerance, degrees | ±8 | ±8 |
| Beamwidth, Vertical, degrees | 5.4 | 4.1 |
| Beamwidth, Vertical Tolerance, degrees | ±0.5 | ±0.5 |
| CPR at Sector, dB | 10 | 10 |
| Front-to-Back Total Power at 180° ± 30°, dB | 30 | 25 |
| USLS (First Lobe), dB | 18 | 18 |
| Input Power per Port, maximum, watts | 300 | 25 |

Mechanical Specifications

| | |
|----------------------------------|---|
| Wind Loading @ Velocity, maximum | 1,253.0 N @ 150 km/h (281.7 lbf @ 150 km/h) |
| Wind Speed, maximum | 250 km/h (155 mph) |

Packaging and Weights

| | |
|---------------|--------------------|
| Width, packed | 427 mm 16.811 in |
|---------------|--------------------|

HHT4-65B-R2

| | |
|-----------------------|---------------------|
| Depth, packed | 304 mm 11.969 in |
| Length, packed | 1931 mm 76.024 in |
| Weight, gross | 36 kg 79.366 lb |

Regulatory Compliance/Certifications

Agency

ISO 9001:2015



Classification

Designed, manufactured and/or distributed under this quality management system

Included Products

- | | | |
|----------|---|--|
| BSAMNT-3 | - | Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set. |
|----------|---|--|

* Footnotes

Performance Note

Severe environmental conditions may degrade optimum performance

BSAMNT-3



Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set.

Product Classification

Product Type Downtilt mounting kit

General Specifications

Application Outdoor

Color Silver

Dimensions

Compatible Diameter, maximum 115 mm | 4.528 in

Compatible Diameter, minimum 60 mm | 2.362 in

Weight, net 6.2 kg | 13.669 lb

Material Specifications

Material Type Galvanized steel

Packaging and Weights

Included Brackets | Hardware

Packaging quantity 1

Weight, gross 6.4 kg | 14.11 lb

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CE | Compliant with the relevant CE product directives |
| CHINA-ROHS | Below maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

BSAMNT-3

