760241905 | MFPS-KXD-P-CQL2-096-30-OK



MFPS Fiber Optic panel, 1RU, 96 fibers/RU, pre-cabled I/O LSZH, 10m, front patch cords orientation to the right, 96 LC/APC, grade C

- Compatible with most common cable types: loose tube, central core, slotted core
- Suitable for cabinets and POP locations
- Various available panel heights to support termination counts from 12 to 288
- Simple wrap-around design for easy fiber routing
- Supports path cord diameters of 1.2 to 2.4mm (XD-series require the usage of 1.2mm patch cords)

Product Classification

Regional Availability EMEA

Portfolio CommScope®

Product Type Fiber patch panel, with indoor/outdoor cable

Product Series MFPS

General Specifications

Functionality Patching

Cable Exit Location Side

Cable Stub Type Indoor/outdoor, stranded

Color Gray

Door Type, frontCompression latch | Hinged

Growth ConfigurationFully loadedInterface, frontLC/APCInterface, rearStub tail

Patch Cord Entry LocationFront, right sidePatch Cord RoutingRight sided

Rack Type EIA 19 in | ETSI 600 mm

Rack Units 1

Shelf Movement Hinged

Total Ports, quantity 96

Transmission Standards ETSI EN 300 019-1-3 | IEC 61300-3-34

Dimensions

COMMSC PE°

760241905 | MFPS-KXD-P-CQL2-096-30-OK

Height 44.45 mm | 1.75 in

Width 482.6 mm | 19 in


Depth 279.91 mm | 11.02 in

Cable Length 30 m | 98.425 ft

Port Configuration

MFPS Capacities		48		72	96
Connector Type		SC	LC	LC	LC Adapter Pack
19 inch	1HU	48	48	72	96
	2HU	96	96	144	192
	2.8 HU	144	144	216	288

Ordering Tree



760241905 | MFPS-KXD-P-CQL2-096-30-OK

Material Specifications

Finish Powder coated

Material Type Ethylene-propylene (EP) | Polyethylene terephthalate (PET)

Optical Specifications

Fiber ModeSinglemodeFiber TypeG.657.A1

Performance Grade Standard C grade

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Storage Temperature $-20 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ (-4 $^{\circ}\text{F}$ to $+176 \,^{\circ}\text{F}$)

EN50575 CPR Cable EuroClass Fire Performance Dca

Flammability Rating UL 94 V-0

Compliant/Exempted

Packaging and Weights

Included Mounting hardware | One cable termination kit

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted



* Footnotes

Performance Grade Guarantee to meet IEC 61755-1 Random Mating requirement

