



ITEM	PART NO.	DESCRIPTION	QTY.	WEIGHT
1	MTC79021020.02	20' SIDE HANDRAIL	4	73.67 LBS
2	MTC79021020.03	20' SIDE TOEBOARD	2	67.05 LBS
3	MTC79021010.05	10' CENTER HANDRAIL	4	35.01 LBS
4	MTC79021010.04	10' CENTER TOEBOARD	2	32.23 LBS
5	EQHR01	HANDRAIL POST	22	15.52 LBS
6	GB-05205	5/8" X 2" GALV BOLT KIT	134	0.27 LBS
7	GW-05	5/8" GALV FLAT WASHER	268	0.06 LBS
8	MTC790208	HANDRAIL ANGLE CLIP	12	1.87 LBS

REVISIONS				
REV.	ECN	DESCRIPTION	BY	DATE
A		INITIAL RELEASE	ACG	11/14/06
B	8000008700	REPLACED MTC790204 WITH EQHR01; UPDATED BOM	RJC	6/15/2015



DETAIL A

<small>These drawings and specifications are the proprietary property of ANDREW CORPORATION and may be used only for the specific purpose authorized in writing by Andrew Corporation.</small>		DRAWN BY: ACG CHECKED BY: TP DATE: 11/14/06 REVISION: B	SHEET: 1 of 1 SCALE: NTS WEIGHT: 1062.25 LBS PART NUMBER: EQ-HR1020 DESCRIPTION: 10' X 20' PLATFORM HANDRAIL DRAWING TYPE: ASSEMBLY DRAWING PART: GALV A123 WEIGHT: 1062.25 LBS	 ORLAND PARK, IL. 60462 U.S.A.
--	--	--	--	--------------------------------------

ALL DIMENSIONS ARE IN INCHES U.O.S.
 TOLERANCES UNLESS OTHERWISE SPECIFIED:
 .X = .06 ANGLES 2'
 .XX = .03 FRACTIONS 1/32
 .XXX = .010
 REMOVE BURRS AND BREAK EDGES .005
 DO NOT SCALE THIS PRINT