# 884046954/16 | CS44Z3 WHT C6A 4/23 F/UTP RL 500M



CS44Z3 ETL Verified Category 6A F/UTP Cable, low smoke zero halogen, white jacket, 4 pair count, 1640 ft (500 m) length, reel

#### **Product Classification**

Regional Availability EMEA

Portfolio NETCONNECT®

Product Type Twisted pair cable

General Specifications

Product Number CS44Z3

ANSI/TIA Category 6A

Cable Component Type Horizontal

**Cable Type** F/UTP (shielded)

Conductor Type, singlesSolidConductors, quantity8Drain Wire TypeSolidJacket ColorWhitePairs, quantity4

Separator Type Isolator

**Transmission Standards** ANSI/TIA-568.2-D

**Dimensions** 

 Cable Length
 500 m | 1,640.42 ft

 Diameter Over Jacket, nominal
 7.518 mm | 0.296 in


 Jacket Thickness
 0.508 mm | 0.02 in

Conductor Gauge, singles23 AWGDrain Wire Gauge26 AWG



# 884046954/16 | CS44Z3 WHT C6A 4/23 F/UTP RL 500M

## Cross Section Drawing



### **Electrical Specifications**

dc Resistance Unbalance, maximum 4 %

dc Resistance, maximum 8 ohms/100 m | 2.438 ohms/100 ft

Mutual Capacitance at Frequency 5.6 nF/100 m @ 1 kHz

Nominal Velocity of Propagation (NVP) 69 %

**Operating Frequency, maximum** 500 MHz

Operating Voltage, maximum 80 V

**Remote Powering** Fully complies with the recommendations set forth by IEEE 802.3bt (Type

4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA

TSB-184-A

С

Segregation Class



# 884046954/16 | CS44Z3 WHT C6A 4/23 F/UTP RL 500M

#### Flectrical Cable Performance

**CS** CommScope

STD Refers to the standard value listed under Transmission Standards in the Electrical Specifications above

TYP Typical Electrical Performance

IL Insertion Loss (dB/100m) NEXT Near End Crosstalk (dB/100m)

 ACR
 Attenuation to Crosstalk Ratio (dB/100m)
 PSNEXT
 Power Sum Near End Crosstalk (db/100m)

 PSACR
 Power Sum Attenuation to Crosstalk Ratio (dB/100m)
 ACRF
 Attenuation to Crosstalk Ratio - Far End (dB/100m)

PSACRF Power Sum Attenuation to Crosstalk Ratio - Far End (dB/100m) RL Return Loss (dB)

TCL Transverse Conversion Loss (dB/100m) ELTCTL Equal Level Transverse Conversion Transfer Loss (dB/100m)

Freq. MHz	IL		NEXT		ACR		PSNEXT		PSACR		ACRF		PSACRF		RL	
	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP
1	2.1	1.7	74.3	90.8	72.2	89.1	72.3	89.1	70.2	87.4	67.8	91.1	64.8	89.1	20	33.8
4	3.8	3.3	65.3	81.1	61.5	77.8	63.3	79.3	59.5	76	55.8	79.7	52.8	77.8	23	34.6
8	5.3	4.6	60.8	76.1	55.4	71.5	58.8	74.3	53.4	69.7	49.7	73.9	46.7	71.9	24.5	36.6
10	5.9	5.2	59.3	75	53.4	69.8	57.3	73	51.4	67.9	47.8	71.9	44.8	70	25	37.2
16	7.5	6.6	56.2	71	48.8	64.5	54.2	69.1	46.8	62.5	43.7	67.7	40.7	65.7	25	37.3
20	8.4	7.4	54.8	69.6	46.4	62.3	52.8	67.8	44.4	60.4	41.8	65.9	38.8	63.8	25	36
25	9.4	8.2	53.3	68.1	44	59.8	51.3	66.2	42	57.9	39.8	63.8	36.8	61.8	24.3	35
31.25	10.5	9.2	51.9	65.8	41.4	56.6	49.9	64.1	39.4	54.9	37.9	61.9	34.9	59.7	23.6	34
62.5	15	13	47.4	60.9	32.4	47.9	45.4	59.2	30.4	46.2	31.9	55.1	28.9	53	21.5	30.4
100	19.1	16.5	44.3	58.3	25.2	41.8	42.3	56.5	23.2	40	27.8	51.8	24.8	49.9	20.1	27.8
155	24.1	20.7	41.4	55.7	17.4	35	39.4	53.7	15.4	33.1	24	48.3	21	46.1	18.8	24.2
200	27.6	23.6	39.8	53.3	12.2	29.7	37.8	51.5	10.2	27.9	21.8	45.6	18.8	43.6	18	22.7
250	31.1	26.4	38.3	52	7.3	25.6	36.3	50	5.3	23.6	19.8	44.7	16.8	42.6	17.3	21.2
300	34.3	29.1	37.1	50	2.9	21	35.1	48	0.9	18.9	18.3	42.2	15.3	40.2	16.8	20
350	37.2	31.5	36.1	48.3	-1.1	16.8	34.1	46.5	-3.1	15	16.9	39.8	13.9	37.8	16.3	19.1
400	40.1	33.9	35.3	47.3	-4.8	13.4	33.3	45.5	-6.8	11.6	15.8	39.5	12.8	37.2	15.9	18
500	45.3	38.1	33.8	45.9	-11.4	7.8	31.8	44	-13.4	5.9	13.8	36.5	10.8	34.2	15.2	16.6

# Material Specifications

Conductor Material Bare copper

**Drain Wire Material** Tinned copper

**Insulation Material** Polyolefin

Jacket Material Low Smoke Zero Halogen (LSZH)

Separator Material Polyolefin

Shield (Tape) Material Polyester/Aluminum shield

Mechanical Specifications

**Pulling Tension, maximum** 11.34 kg | 25 lb



# 884046954/16 | CS44Z3 WHT C6A 4/23 F/UTP RL 500M

### **Environmental Specifications**

Installation temperature 0 °C to +60 °C (+32 °F to +140 °F)

**Operating Temperature**  $-20 \, ^{\circ}\text{C} \text{ to } +60 \, ^{\circ}\text{C} \text{ (-4 } ^{\circ}\text{F to } +140 \, ^{\circ}\text{F)}$ 

Acid Gas Test Method IEC 60754-2

EN50575 CPR Cable EuroClass Fire PerformanceDcaEN50575 CPR Cable EuroClass Smoke Ratings2EN50575 CPR Cable EuroClass Droplets Ratingd2EN50575 CPR Cable EuroClass Acidity Ratinga1

Environmental Space Low Smoke Zero Halogen (LSZH)

Flame Test Method IEC 60332-3-22
Smoke Test Method IEC 61034-2

Packaging and Weights

**Cable weight** 52.309 kg/km | 35.15 lb/kft

Packaging Type Reel

### Regulatory Compliance/Certifications

Agency	Classification
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

