

7680813 | SFP+LR, up to 10 km



Small Form-Factor Pluggable+ Module, 10G BASE, Singlemode

Product Classification

Product Type	Optical module
Product Series	SFP+

General Specifications

Interface	LC/UPC
Note	Detailed Product Specifications are available. Please contact your local ANDREW representative.

Dimensions

Height	13 mm 0.512 in
Width	13.9 mm 0.547 in
Depth	56.4 mm 2.22 in

Optical Specifications

Fiber Type	9/125 μ m, singlemode
Average Optical Output Power, maximum	0.5 dBm
Average Optical Output Power, minimum	-8.2 dBm
Rx/Tx Power Accuracy	\pm 3dB / \pm 3dB
Operating Wavelength	1260 – 1360 nm 1260 – 1610 nm (Rx)
Receiver Sensitivity, maximum	-14.4 dBm
Receiver Overload	+ 0.5 dBm

Environmental Specifications

Operating Temperature	0 °C to +70 °C (+32 °F to +158 °F)
------------------------------	------------------------------------

Packaging and Weights

Height, packed	20 mm 0.787 in
-----------------------	------------------

7680813 | SFP+LR, up to 10 km

Width, packed	105 mm 4.134 in
Depth, packed	65 mm 2.559 in
Packaging quantity	1
Packaging Type	Box
Weight, gross	0.036 kg 0.079 lb
Weight, net	0.022 kg 0.049 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

