BC1BBB2

Base Product



Uniprise Category 6 U/UTP Patch Cord, RJ45 to RJ45, 4-pair, Non-Plenum (Pack of 10)

Product Classification

Regional Availability

North America

Portfolio Uniprise®

Product TypeTwisted pair patch cord

Product Series BC

Ordering Note Cords < 1 m are valid elements for use in a channel or as an equipment interconnect

but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords | Cords > 1 m are authorized for use in channels and are an effective standalone method used to

connect active devices

General Specifications

ANSI/TIA Category 6

Cable Type U/UTP (unshielded)

Conductor TypeStrandedInterface, Connector ARJ45 plugInterface Feature, connector AStandardInterface, Connector BRJ45 plugInterface Feature, connector BStandard

Jacket Color Black | Blue | Green | Orange | Purple | Red | Slate | Violet | White | Yellow

Pairs, quantity 4

Transmission Standards IEEE 802.3bt Type 4

Wiring T568B

Dimensions

Cable Assembly Length Range (m)1-8Cable Assembly Length Range (ft)1-25

Page 1 of 3

BC1BBB2

Cable Assembly Length Range (cm)15 - 800Cable Assembly Length Range (in)6 - 300

Diameter Over Jacket 5.97 mm | 0.235 in

Compatible Conductor Gauge, stranded 24 AWG

Wiring Diagram

	Connector A	Connector B
Position 1	White/Orange	White/Orange
Position 2	Orange	Orange
Position 3	Lt. Green	Lt. Green
Position 4	Blue	Blue
Position 5	Lt. Blue	Lt. Blue
Position 6	Green	Green
Position 7	Lt. Brown	Lt. Brown
Position 8	Brown	Brown


Electrical Specifications

dc Resistance, maximum0.3 ohmSafety Voltage Rating300 V

Ordering Tree



BC1BBB2



UOM

11		Foot	
	М	Meter	
	N	Inch	

Length

Notes

- Cords > 1m are authorized for use in channels and are an effective standalone method used to connect active devices
- Cords < 1m are also valid elements for use in a channel or as an equipment interconnect but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords

Material Specifications

Contact Plating Material Precious metals

Material Type Copper alloy | Polycarbonate

Mechanical Specifications

Plug Insertion Life, minimum 750 times

Plug Retention Force, minimum 133 N | 29.9 lbf

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \text{ (+14 °F to +140 °F)}$

Environmental SpaceNon-plenumFlammability RatingUL 94 V-0Safety StandardETL | cETL

Packaging and Weights

Packaging quantity 10

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

COMMSCOPE®