

UHF Male to UHF Female Right Angle Adapter



OBSOLETE

Product Classification

Product Type Adapter

General Specifications

Body Style Right angle

Inner Contact Plating Silver

Interface UHF Male

Interface 2 UHF Female

Mounting Angle Right angle

Outer Contact Plating Nickel

Pressurizable No

Dimensions


Width 31.75 mm | 1.25 in

Length 31.75 mm | 1.25 in

Diameter 19.05 mm | 0.75 in

Outline Drawing

10805-5



Electrical Specifications

Average Power at Frequency	300.0 W @ 900 MHz
Connector Impedance	50 ohm
dc Test Voltage	2000 V
Inner Contact Resistance, maximum	5 mOhm
Insulation Resistance, minimum	5000 MOhm
Operating Frequency Band	0 – 300 MHz
Outer Contact Resistance, maximum	5 mOhm

Mechanical Specifications

Interface Durability	500 cycles
Interface Durability Method	IEC 61169-12:9.5
Mechanical Shock Test Method	IEC 60068-2-27

Environmental Specifications

Operating Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
Storage Temperature	-65 °C to +125 °C (-85 °F to +257 °F)
Attenuation, Ambient Temperature	20 °C 68 °F
Average Power, Ambient Temperature	40 °C 104 °F

10805-5

Average Power, Inner Conductor Temperature	100 °C 212 °F
Climatic Sequence Test Method	IEC 60068-1
Corrosion Test Method	IEC 60068-2-11
Damp Heat Steady State Test Method	IEC 60068-2-3
Thermal Shock Test Method	IEC 60068-2-14
Vibration Test Method	IEC 60068-2-6

Packaging and Weights

Weight, net	36 g 0.079 lb
--------------------	-----------------