



SL-Series Modular Jack, RJ45, Cat6 Unshielded, Black

Product Classification

Regional Availability	North America
Portfolio	Uniprise®
Product Type	Modular jack
Product Series	USL Series

General Specifications

ANSI/TIA Category	6
Cable Type	Unshielded
Color	Black
Conductor Type	Solid Stranded
Integrated Dust Cover Type	None
Mounting Note	Color matches with SL-style Black Faceplates and Surface Mount Boxes
Termination Type	IDC
Wiring	T568A T568B

Dimensions

Compatible Conductor Gauge, solid	22 AWG 24 AWG
Compatible Conductor Gauge, stranded	24 AWG 26 AWG

Electrical Specifications

Contact Resistance Variation, maximum	20 mOhm
Contact Resistance, maximum	100 mOhm
Current Rating at Temperature	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1,500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1,000 Vac @ 60 Hz
Insulation Resistance, minimum	500 MOhm

760237627 | USL600-BK

Remote Powering

Fully supports the safe delivery of power over LAN cabling described by IEEE 802.3bt (Type 4) and complies with the unmating under electrical load requirements prescribed by IEC 60512-99-002

PoE Durability

Supports IEEE 802.3bt Type 4 (90 W) applications after 3000 plug to jack mating cycles

Material Specifications

Contact Plating Material

Precious metals

Material Type

Copper alloy | High-impact, flame retardant, thermoplastic

Termination Contact Plating

Nickel

Mechanical Specifications

Plug Insertion Life, test plug

IEC 60603-7 compliant plug

Plug Retention Force, minimum

133 N | 29.9 lbf

Plug to Jack Mating Cycles

Complies to IEC 60603-7 series

Environmental Specifications

Operating Temperature

-10 °C to +60 °C (+14 °F to +140 °F)

Storage Temperature

-40 °C to +70 °C (-40 °F to +158 °F)

Relative Humidity

Up to 95%, non-condensing

Flammability Rating

UL 94 V-0

Safety Standard

UL | cUL

Packaging and Weights

Packaging quantity

1

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

