

760242346 | MFC-SCF-UNV-5X QWIK II™ SC



Qwik II® Field Installable SC Connector, OM3/4/5, Aqua, for 0.25/0.9/2.0 /3.0 mm, single pack

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber connector
Product Brand	LazrSPEED® Qwik II®
Product Series	Qwik II

General Specifications

Body Style	Universal
Color, boot	Black
Color, housing	Aqua
Ferrule Geometry	Factory polished
Interface	SC/UPC
Interface Feature	Field Installable Mechanical splice

Dimensions

Compatible Cable Diameter	0.25 mm 0.01 in 0.9 mm 0.035 in 2 mm 0.079 in 3 mm 0.118 in
----------------------------------	---------------------------------------------------------------------------

Material Specifications

Ferrule Material	Zirconia
-------------------------	----------

Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM3 OM4 OM5, LazrSPEED® wideband
Insertion Loss, maximum	0.5 dB
Insertion Loss, typical	0.1 dB

760242346 | MFC-SCF-UNV-5X QWIK II™ SC

Return Loss, minimum 20 dB

Environmental Specifications

Operating Temperature -40 °C to +75 °C (-40 °F to +167 °F)

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Above maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant/Exempted

UK-ROHS

Compliant/Exempted

