# CT-15-TUW-NI6



#### 15 dB, Tapper, 340 – 6000 MHz

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type Tapper

General Specifications

**Device Type** Tapper

**Application** Indoor/Outdoor

ColorWhiteInner Contact PlatingSilverInterfaceN Female

Outer Contact Plating Trimetal

**Dimensions** 

 Height
 25 mm | 0.984 in

 Width
 43 mm | 1.693 in

 Length
 141 mm | 5.551 in

**Electrical Specifications** 

**3rd Order IMD** -163 dBc

**3rd Order IMD Test Method** Two +43 dBm carriers

Insertion Loss at Frequency Band 0.35 dB @ 1695-2700 MHz | 0.35 dB @ 340-960 MHz | 0.4 dB @ 3500-4500

MHz | 0.4 dB @ 4900-6000 MHz

**Return Loss at Frequency Band** 19.1 dB @ 3500-4500 MHz | 19.1 dB @ 4900-6000 MHz | 20.8 dB @ 1695-2700

MHz | 20.8 dB @ 340-960 MHz

Average Power, maximum 200 W

**Coupling** 15 dB

**Coupling Tolerance** +0.3/-1.3dB @ 3500-4500 MHz | ±0.6dB @ 1695-2700 MHz | ±0.7dB @ 698-960

MHz | ±0.8dB @ 380-520 MHz | ±0.8dB @ 4900-6000 MHz | ±1.0dB @ 340-380 MHz

**Impedance** 50 ohm

Page 1 of 2

## CT-15-TUW-NI6

**Operating Frequency Band** 1695 – 2700 MHz | 340 – 960 MHz | 3500 – 4500 MHz | 4900 – 6000 MHz

Peak Power, maximum 3 kW
Reflected Power, maximum 200 W

Mechanical Specifications

**Coupling Nut Proof Torque** 4.5 N-m | 39.828 in lb

#### **Environmental Specifications**

**Operating Temperature**  $-35 \,^{\circ}\text{C}$  to  $+85 \,^{\circ}\text{C}$  (-31  $^{\circ}\text{F}$  to  $+185 \,^{\circ}\text{F}$ )

**Relative Humidity** Up to 100%

Corrosion Test Method IEC 60068-2-11, 30 days
Ingress Protection Test Method IEC 60529:2001, IP67

#### Packaging and Weights

 Height, packed
 40 mm | 1.575 in

 Width, packed
 90 mm | 3.543 in

 Length, packed
 180 mm | 7.087 in

 Weight, gross
 300 g | 0.661 lb

 Weight, net
 250 g | 0.551 lb

### Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant

UK-ROHS Compliant/Exempted





