

# H5NF-T

Tunable N Female with gas barrier for 7/8 in HJ5-50 air dielectric cable



## OBSOLETE

### Replaced By:

H5PNF

Type N Female with gas barrier for 7/8 in HJ5-50 air dielectric cable

## Product Classification

<b>Product Type</b>	Air coaxial connector
<b>Product Brand</b>	HELIAX®

## General Specifications

<b>Body Style</b>	Straight
<b>Cable Family</b>	HJ5-50
<b>Gas Barrier</b>	Yes
<b>Inner Contact Attachment Method</b>	Self-tapping
<b>Inner Contact Plating</b>	Silver
<b>Interface</b>	N Female
<b>Mounting Angle</b>	Straight
<b>Outer Contact Attachment Method</b>	Tab-flare
<b>Outer Contact Plating</b>	Unplated

## Dimensions

<b>Length</b>	208.026 mm   8.19 in
<b>Diameter</b>	35.814 mm   1.41 in
<b>Nominal Size</b>	7/8 in

## Electrical Specifications

# H5NF-T

---

<b>Insertion Loss, typical</b>	0.05 dB
<b>Average Power at Frequency</b>	0.6 kW @ 900 MHz
<b>Cable Impedance</b>	50 ohm
<b>Connector Impedance</b>	50 ohm
<b>dc Test Voltage</b>	2 kV
<b>Insulation Resistance, minimum</b>	5000 MOhm
<b>Operating Frequency Band</b>	0 – 5200 MHz
<b>Peak Power, maximum</b>	10 kW
<b>RF Operating Voltage, maximum (vrms)</b>	707 V

## VSWR/Return Loss

<b>Frequency Band</b>	<b>VSWR</b>	<b>Return Loss (dB)</b>
<b>1700–2300 MHz</b>	1.12	25
<b>2300–2700 MHz</b>	1.12	25

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +150 °C (-40 °F to +302 °F)
<b>Storage Temperature</b>	-70 °C to +100 °C (-94 °F to +212 °F)

## Packaging and Weights

<b>Weight, net</b>	0.93 kg   2.05 lb
--------------------	-------------------

## \* Footnotes

<b>Insertion Loss, typical</b>	0.05v <sup>-</sup> freq (GHz) (not applicable for elliptical waveguide)
--------------------------------	---