

Standard Grounding Kit for 2-1/4 in and 3 in corrugated coaxial cable and elliptical waveguide 28 and 37

Product Classification

Product Type Grounding kit

Ordering Note CommScope® non-standard product

General Specifications

Bonding Conductor Jacketing MaterialPVCBonding Conductor MaterialCopperBonding Conductor Wire Size6 gauge

Cable Type Corrugated | Elliptical waveguide

Color Black

Grounding Kit Type Standard Grounding Kits

Grounding Strap Material Copper

Lug AttachmentField attachedLug TypeTwo-hole lug

Thread Size 3/8 in

Dimensions

Bonding Conductor Length1524 mm | 60 inCable Jacketing Removal Length, maximum58.42 mm | 2.3 inCable Jacketing Removal Length, minimum55.88 mm | 2.2 inCompatible Diameter, maximum78.74 mm | 3.1 inCompatible Diameter, minimum58.674 mm | 2.31 in

Nominal Size 2-1/4 in | 3 in

Waveguide Size WR229 | WG11 | R40 | WR284 | WG10 | R32

Electrical Specifications

Current Handling Tested to withstand 100,000 amps peak current surge

Current Handling Test Method MIL-STD-1757

COMMSCOPE®

Grounding, Bonding and Shielding Test Method MIL-STD-188-124A

Lightning Protection Test MethodIEC 1024-1

Material Specifications

Rivet Material Copper

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

Storage Temperature $-40 \,^{\circ}\text{C} \text{ to } +80 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +176 \,^{\circ}\text{F})$

Blowing Rain Test Method MIL-STD-810, Method 506

Corrosion Test Method MIL-STD-1344, Method 1001

Freezing Rain/Icing Test Method MIL-STD-810, Method 521

Humidity Test Method MIL-STD-1344, Method 1002

Immersion Test Method IEC 60529:2001, IP68

UV Resistance Test Method MIL-STD-810, Method 505

Vibration Test Method MIL-STD-202, Method 214

Weatherproofing Method Butyl and electric tape

Packaging and Weights

 Height, packed
 269.24 mm | 10.6 in

 Width, packed
 58.42 mm | 2.3 in

Length, packed 177.8 mm | 7 in

Included Grounding kit | Hardware | Lug | One roll of 2 in PVC tape | One

roll of 24 in butyl rubber tape

Packaging quantity 1

Weight, gross 0.92 kg | 2.028 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant





Included Products

42615-10 - Butyl Rubber Tape, 24 in - Black 2 in PVC Tape, 20 ft 9905-71

* Footnotes

Grounding, Bonding and Shielding Test Method Military Standard for Grounding, Bonding, and Shielding: Bond Resistance

Requirement of a Maximum dc resistance of 0.001 ohm

Lightning Protection Test Method Protection Against Lightning Electromagnetic Impulse, Table 1—Protection

Level III-IV, 1995-02





Page 3 of 7



Butyl Rubber Tape, 24 in

Product Classification

Product TypeWeatherproofing tape

Ordering Note CommScope® non-standard product

General Specifications

Application Provides additional moisture seal for cable connections

Applications per KitOne 1/2 in-2-1/4 in | One 1/2 in-7/8 in | One 1/2 in-7/8 in to

device | Two 1/2 in-1/2 in

Color Black

Dimensions

 Width
 63.5 mm | 2.5 in

 Length
 609.6 mm | 24 in

Nominal Size 1-1/4 in | 1-5/8 in | 1/2 in | 1/4 in | 2-1/4 in | 3/8 in | 5/8 in | 7

/8 in

Material Specifications

Material Type Butyl rubber tape

Environmental Specifications

UV Resistance Test MethodButyl test method in QUV weatherometer cycle of 8 hours UV at 150 °F then 4

hours of condensation at 104 °F

UV Resistance, minimum with no degradation ≥1000 hours

Weather Resistance Test Method 04AS00-03.6.0 | MIL-STD-1344A, Method 1002

Packaging and Weights

 Height, packed
 63.5 mm | 2.5 in

 Width, packed
 71.12 mm | 2.8 in

 Length, packed
 25.4 mm | 1 in

Page 4 of 7



Packaging quantity

1

Weight, gross

0.17 kg | 0.375 lb

Regulatory Compliance/Certifications

Agency

Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system





Black 2 in PVC Tape, 20 ft

Product Classification

Product Type Weatherproofing tape

Ordering Note CommScope® non-standard product

General Specifications

Application Provides additional moisture seal for cable connections

Applications per Kit Four 1/2 in -1/2 in | Four 1/2 in -7/8 in to device | One 1/2 in -2-1/4 in | Two 1/2 in -7/8

in

Color Black

Dimensions

 Width
 50.8 mm | 2 in

 Length
 6096 mm | 240 in

Nominal Size 1-1/4 in | 1-5/8 in | 1/2 in | 1/4 in | 2-1/4 in | 3/8 in | 5/8 in | 7/8 in

Material Specifications

Material Type PVC tape

Environmental Specifications

UV Resistance Test Method PVC tape test method UL 510, ASTM D1000

Weather Resistance Test Method 04AS00-03.6.0 | MIL-STD-1344A, Method 1002

Packaging and Weights

 Height, packed
 63.5 mm | 2.5 in

 Width, packed
 63.5 mm | 2.5 in

 Length, packed
 50.8 mm | 2 in

Packaging quantity 1

Weight, gross 0.08 kg | 0.176 lb

Page 6 of 7

Regulatory Compliance/Certifications

Agency

Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

