

BHD-38



Double Block Hanger for 3/8 in coaxial cable

Product Classification

Product Type Hanger kit

General Specifications

Cables per Hanger 2

Color Black

Hanger Type Double block hanger

Mounting Mounting hole clearance for 3/8, 16 UNC or M10 threaded rod

Dimensions

Maximum Stack Height 3

Height 36.1 mm | 1.421 in

Width 24.1 mm | 0.949 in

Length 42.9 mm | 1.689 in

Compatible Cable Diameter Range 10–12 mm

Compatible Diameter, maximum 12 mm | 0.472 in

Compatible Diameter, minimum 10 mm | 0.394 in

Nominal Size 3/8 in

Electrical Specifications

Return Loss Effect, maximum 0.1 dB

DTF Effect, maximum 0.1 dB

Material Specifications

Material Type Engineered plastic

BHD-38

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Environmental Strength Capability	Double cable weight
UV Resistance, minimum with no degradation	≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed	3.8 cm 1.496 in
Width, packed	12.7 cm 5 in
Length, packed	17.8 cm 7.008 in
Packaging quantity	10
Weight, gross	0.14 kg 0.309 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power