

FA-1923-STH



Standard Butterfly Hanger and Grommet kit for HELIAX® Cables, 19-23mm

Product Classification

Product Type	Hanger kit
Ordering Note	CommScope® non-standard product

General Specifications

Cables per Hanger	1
Color	Black Silver
Hanger Type	Hanger kits
Mounting	3/8 in (M10) drilled cable ladder

Dimensions

Maximum Stack Height	0
Height	58.9 mm 2.319 in
Width	38.1 mm 1.5 in
Length	76.2 mm 3 in
Compatible Cable Diameter Range	19–23 mm
Compatible Diameter, maximum	23 mm 0.906 in
Compatible Diameter, minimum	19 mm 0.748 in
Nominal Size	1-1/4 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	EPDM rubber Stainless steel
----------------------	-------------------------------

FA-1923-STH

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Corrosion Resistance, minimum with no degradation ≥500 hours in salt spray chamber

Environmental Strength Capability Double cable weight

Packaging and Weights

Height, packed 26 cm | 10.236 in

Width, packed 9 cm | 3.543 in

Length, packed 9 cm | 3.543 in

Packaging quantity 10

Weight, gross 0.53 kg | 1.168 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power