

# FA-5MM-12-AD

---



1/2 in Double Hanger Kit for HELIAX® tails, 5 mm grommet, angle adapter, triple stack, kit of 10

## Product Classification

<b>Product Type</b>	Hanger kit
<b>Ordering Note</b>	CommScope® non-standard product

## General Specifications

<b>Cables per Hanger</b>	6
<b>Color</b>	Black
<b>Hanger Type</b>	Composite clamp
<b>Mounting</b>	M8 hardware

## Dimensions

<b>Maximum Stack Height</b>	3
<b>Height</b>	78 mm   3.071 in
<b>Width</b>	25.9 mm   1.02 in
<b>Length</b>	66 mm   2.598 in
<b>Compatible Cable Diameter Range</b>	15.2–16.3 mm
<b>Compatible Diameter, maximum</b>	16.3 mm   0.642 in
<b>Compatible Diameter, minimum</b>	15.2 mm   0.598 in

## Material Specifications

<b>Material Type</b>	Corrosion proof coated metal   Engineered plastic
----------------------	---

## Mechanical Specifications

<b>Vibration Survival</b>	≥4 hours at resonant frequency
---------------------------	--------------------------------

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
<b>Corrosion Resistance, minimum with no degradation</b>	≥500 hours in salt spray chamber

# FA-5MM-12-AD

---

**Environmental Strength Capability**

Double cable weight

**UV Resistance, minimum with no degradation**

≥100 hours exposure in accelerated UV life chamber

## Packaging and Weights

**Packaging quantity**

10

## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power