CX3399697 | 125G135 EMPTY DUCT COEX



ConQuest® Empty Conduit, 1 1/4 in, SDR 13.5, gray

Product Classification

Product TypeEmpty conduitProduct BrandConQuest®

General Specifications

Color Gray

Conduit TypeNon-toneableDensity Test MethodASTM D792A

 Density, maximum
 0.955 g/cm³ | 0.035 lb/in³

 Density, minimum
 0.941 g/cm³ | 0.034 lb/in³

Design Standard ASTM D3350-05

Wall Type Smooth

Dimensions

Length 914.4 m | 3000 ft

 Inner Diameter, nominal
 35.408 mm | 1.394 in

 Outer Diameter, nominal
 42.164 mm | 1.66 in

Wall Thickness Designation SDR 13.5

Wall Thickness, minimum 3.124 mm | 0.123 in

Nominal Size 1-1/4 in

Material Specifications

Flexural Modulus, minimum 551.581 N/mm² | 80000 psi

Flexural Property Test Method ASTM D790

Hydrostatic Design BasisNot pressure rated

Hydrostatic Design Test Method ASTM D2837

Material Type High density polyethylene (HDPE)

Melt Flow Rate Test Method ASTM D1238

Page 1 of 2

CX3399697 | 125G135 EMPTY DUCT COEX

Melt Flow Rate, maximum 0.39 g/10 min

Mechanical Specifications

Minimum Bend Radius, unsupported 457.2 mm | 18 in

Tensile Property Test Method ASTM D638

Tensile Strength at yield, minimum 20.684 N/mm² | 3000 psi

Pulling Tension, maximum 571.526 kg | 1260 lb

Environmental Specifications

Environmental Stress Crack Resistance Failure rate of 10% within 96 hours

Environmental Stress Test Method ASTM D1693, ESCR Condition B

Packaging and Weights

Weight, net 394.363 kg/km | 265 lb/kft

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

* Footnotes

Environmental Stress Crack Resistance ESCR—Environmental Stress Crack Resistence

