## ST-SVP40



## Solar/Video Embedded Communication Pole, 40 ft

- Hinged design
- No climbing necessary for equipment installation
- Single person service
- Secure locking

## Product Classification

**Product Type** 

Monopole

## General Specifications

Application	Solar   Supervisory Control and Data Acquisition (SCADA)/Video surveillance
Equipment Load Rating	Omni antenna   Solar panel   Telecommunications unit
Foundation	Embedded
Monopole Capability Type	Light duty
Monopole Design	Round conical
Optional Accessories	Antenna mounts   Ballast mounting kit   Cabinet mounts   Solar mounts   Video mounts
Dimensions	
Height	12.192 m   40 ft
Mounting Diameter, maximum	276.86 mm   10.9 in
Mounting Diameter, minimum	114.3 mm   4.5 in
Material Specifications	
Material Type	Hot dip galvanized steel
Mechanical Specifications	
Wind Rating Test Method	TIA/EIA-222-G
Packaging and Weights	
Included	Ground tab   Hand holes   Lightning rod   Monopole

IncludedGround tab| Hand holes| Lightning rod| MonopolePackaging quantity1Weight, net211.1 kg | 465.395 lb

Page 1 of 1



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025