

244106A-120



Flex-Twist Hanger Assembly for WR75

Product Classification

Product Type Hanger kit

General Specifications

Cable Type Elliptical waveguide

Cables per Hanger 1

Color Silver

Hanger Type Flex-Twist hanger

Mounting 4.5 in OD pipe

Dimensions

Height 10.2 mm | 0.402 in

Width 101.6 mm | 4 in

Length 641.4 mm | 25.252 in

Waveguide Size WR75 | WG17 | R120

Material Specifications

Material Type Stainless steel

Mechanical Specifications

Wind Speed, survival with 1/2 in (12 mm) radial ice 201.167 km/h | 125 mph

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Corrosion Test Method MIL-F-14072C | MIL-STD-889B

Packaging and Weights

Included Clamp | Rubber grommet | Threaded rod

244106A-120

Packaging quantity 1
Weight, gross 1.64 kg | 3.616 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system