

244106A-220



Flex-Twist Hanger Assembly for WR42

Product Classification

Product Type Hanger kit

General Specifications

Cable Type Elliptical waveguide

Cables per Hanger 1

Color Silver

Hanger Type Flex-Twist hanger

Mounting 4.5 in OD pipe

Dimensions

Height 7.6 mm | 0.299 in

Width 151.9 mm | 5.98 in

Length 381 mm | 15 in

Waveguide Size WR42 | WG20 | R220

Material Specifications

Material Type Stainless steel

Mechanical Specifications

Wind Speed, survival with 1/2 in (12 mm) radial ice 125 mph | 201.167 km/h

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Corrosion Test Method MIL-F-14072C | MIL-STD-889B

244106A-220

Packaging and Weights

Included	Clamp Rubber grommet Threaded rod
Packaging quantity	1
Weight, gross	0.64 kg 1.411 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

