

# EWSH-63

---



## Universal Snap-in Hanger for elliptical waveguide 63

### Product Classification

**Product Type** Hanger kit

### General Specifications

**Cable Type** Elliptical waveguide

**Cables per Hanger** 1

**Color** Silver

**Hanger Type** Snap-in hanger

**Mounting** 3/4 in through hole

### Dimensions

**Height** 40.9 mm | 1.61 in

**Width** 59.9 mm | 2.358 in

**Length** 89.9 mm | 3.539 in

**Compatible Diameter, maximum** 31 mm | 1.22 in

**Compatible Diameter, minimum** 26.7 mm | 1.051 in

**Waveguide Size** WR137 | WG14 | R70

### Electrical Specifications

**Return Loss Effect, maximum** 0.1 dB

**DTF Effect, maximum** 0.1 dB

### Material Specifications

**Material Type** Stainless steel

### Mechanical Specifications

# EWSH-63

---

## Vibration Survival

≥4 hours at resonant frequency

## Environmental Specifications

### Operating Temperature

-40 °C to +85 °C (-40 °F to +185 °F)

### Corrosion Resistance, minimum with no degradation

≥500 hours in salt spray chamber

### Environmental Strength Capability

Double cable weight

## Packaging and Weights

### Height, packed

20 cm | 7.874 in

### Width, packed

20 cm | 7.874 in

### Length, packed

20 cm | 7.874 in

### Packaging quantity

10

### Weight, gross

1.6 kg | 3.527 lb

## Regulatory Compliance/Certifications

### Agency

### Classification

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

