
## 760172940 | 1091B PRP C6A 4/23 UTP



GigaSPEED X10D® 1091B ETL Verified Category 6A U/UTP Cable, purple jacket, 4 pair count, 1000 ft (305 m) length, WE TOTE® box

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | Latin America | North America

Portfolio SYSTIMAX®

Product Type Twisted pair cable
Product Brand GigaSPEED X10D®

General Specifications

Product Number 1091B
ANSI/TIA Category 6A

Cable Component Type Horizontal

Cable Type U/UTP (unshielded)

Conductor Type, singlesSolidConductors, quantity8Jacket ColorBlackPairs, quantity4

Separator Type Isolator

**Transmission Standards** ANSI/TIA-568.2-D | ISO/IEC 11801 Class EA

**Dimensions** 


Cable Length304.8 m | 1000 ftDiameter Over Insulated Conductor0.864 mm | 0.034 inDiameter Over Jacket, nominal7.239 mm | 0.285 inJacket Thickness1.295 mm | 0.051 in

Conductor Gauge, singles 23 AWG

Cross Section Drawing



### 760172940 | 1091B PRP C6A 4/23 UTP



#### **Electrical Specifications**

dc Resistance, maximum 7.61 ohms/100 m | 2.32 ohms/100 ft

**Dielectric Strength, minimum** 1500 Vac | 2500 Vdc

LP (Limited Power) Rating 0.5 A

Mutual Capacitance at Frequency 6.0 nF/100 m @ 1 kHz

Nominal Velocity of Propagation (NVP) 65 %

Operating Frequency, maximum 550 MHz

Operating Voltage, maximum 80 V

**Remote Powering** Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the

safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2,

CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A

### Material Specifications

 Conductor Material
 Bare copper

 Insulation Material
 Polyolefin

 Jacket Material
 PVC

Page 2 of 3



# 760172940 | 1091B PRP C6A 4/23 UTP

Separator MaterialPolyolefinSeparator 2 MaterialPolyolefin

Mechanical Specifications

**Pulling Tension, maximum** 11.34 kg | 25 lb

**Environmental Specifications** 

Installation temperature  $0 \,^{\circ}\text{C}$  to +60  $^{\circ}\text{C}$  (+32  $^{\circ}\text{F}$  to +140  $^{\circ}\text{F}$ )

Operating Temperature  $-20 \,^{\circ}\text{C}$  to +60  $^{\circ}\text{C}$  (-4  $^{\circ}\text{F}$  to +140  $^{\circ}\text{F}$ )

**Environmental Space**Non-plenum **Temperature Rating, UL**90 °C | 194 °F

Flame Test Method CMR

Packaging and Weights

**Cable weight** 55.509 kg/km | 37.3 lb/kft

Packaging Type WE TOTE® box

