

# BHD-58

---



## Double Block Hanger for 18 to 20mm Cables

### Product Classification

<b>Product Type</b>	Hanger kit
<b>Ordering Note</b>	CommScope® standard product (Global)

### General Specifications

<b>Cables per Hanger</b>	2
<b>Color</b>	Black
<b>Hanger Type</b>	Double block hanger
<b>Mounting</b>	Mounting hole clearance for 3/8, 16 UNC or M10 threaded rod

### Dimensions

<b>Maximum Stack Height</b>	3
<b>Height</b>	27.9 mm   1.098 in
<b>Width</b>	39.6 mm   1.559 in
<b>Length</b>	72.4 mm   2.85 in
<b>Compatible Cable Diameter Range</b>	17.8–20.1 mm
<b>Compatible Diameter, maximum</b>	20.1 mm   0.791 in
<b>Compatible Diameter, minimum</b>	17.8 mm   0.701 in
<b>Nominal Size</b>	5/8 in

### Electrical Specifications

<b>Return Loss Effect, maximum</b>	0.1 dB
<b>DTF Effect, maximum</b>	0.1 dB

### Material Specifications

<b>Material Type</b>	Engineered plastic
----------------------	--------------------

### Environmental Specifications

# BHD-58

---

<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
<b>Environmental Strength Capability</b>	Double cable weight
<b>UV Resistance, minimum with no degradation</b>	≥100 hours exposure in accelerated UV life chamber

## Packaging and Weights

<b>Height, packed</b>	3.8 cm   1.496 in
<b>Width, packed</b>	17.8 cm   7.008 in
<b>Length, packed</b>	25.4 cm   10 in
<b>Packaging quantity</b>	10
<b>Weight, gross</b>	0.45 kg   0.992 lb

## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power