

Mini-OPE 210-Series, Optical Terminal Enclosure, 8-port full-size connector, 1x8 splitter, 12 splice trays, grey, wall mount

- Optical Terminal Enclosures incorporate hardened connector technology that is designed to withstand the rugged outside plant environment
- Functionality to splice and store feeder cable in the field with the possibility to splice in the field two extra branch cables
- Hardened adapters are factory-terminated and environmentally sealed to ensure rapid plug-and-play drop cable installations
- Integrated external cable fixation guarantees easy, fast and reliable cable manipulations

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America
<b>Product Type</b>	Access terminal, without splitter/tap
<b>Product Series</b>	Mini-OPE 200

## General Specifications

<b>Cable Type</b>	No cable (stubless)
<b>Cable, quantity</b>	0
<b>Distribution Type</b>	1 x 8 splitter
<b>Enclosure Color</b>	Gray
<b>Mounting</b>	Handhole   Pole   Wall
<b>Port Type</b>	Hardened full-size SC/APC
<b>Port, quantity</b>	6
<b>Splice Tray Included, quantity</b>	1
<b>Splicing Type, Supported</b>	Single fusion
<b>Split Ratio</b>	Symmetrical
<b>Splitter, quantity</b>	1
<b>Stub Type</b>	No tail

## Dimensions


<b>Height</b>	358.5 mm   14.114 in
<b>Width</b>	166 mm   6.535 in
<b>Depth</b>	129.3 mm   5.091 in

# 760242322 | OTE210-08MH-18-S12-G-W


**Cable Length, stub**

0 ft (0 m)

## Dimension Drawing



## Ordering Tree



## Material Specifications

**Enclosure Material Type**

Glass filled polypropylene (GF-PP)

## Optical Specifications

**Fiber Type**

G.652.D

# 760242322 | OTE210-08MH-18-S12-G-W

<b>Operating Wavelength Range</b>	1260 – 1635 nm
<b>Attenuation Terminal Connectors, maximum</b>	0.4 dB
<b>Insertion Loss, Terminal Connector, typical</b>	0.16 dB
<b>Return Loss, Connector, minimum</b>	65 dB

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +65 °C (-40 °F to +149 °F)
<b>Relative Humidity</b>	5%–100%, condensing
<b>Environmental Space</b>	Above ground   Below ground   Buried
<b>Qualification Standards</b>	IEC 60529, IP68 + 3 m waterhead
<b>UV Resistance</b>	UV stabilized

## Packaging and Weights

<b>Included</b>	Cable termination unit (2)   Enclosure (1)   Fiber pigtail cassette (1)   Splice Cassette (2)
<b>Packaging quantity</b>	1
<b>Packaging Type</b>	Box   Carton

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



## Included Products

CW8094-002 – TENIO™ Cable Termination Unit kit  
TENIO-CTU-L-(10)