


NG4-MMDC20R000



NG4access® MPO Module, multimode OM4, LC-MPO 1x24 fiber, Polarity A, right exit (for MPO module)

- Offers the same craft-friendly interface for LC and SC connectors as the cabled module
- Allow installers to connect an MPO trunk cable to turn up services in rapid installation applications

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber module
Product Brand	NG4access®
Product Series	NG4

General Specifications

Functionality	Breakout
Application	NG4 MPO module
Adapter Color	Aqua
Adapters, quantity, front	12
Body Style	Simplex
Color, front	Black
Color, housing	Black
Color, rear	Black
Interface, front	SC/UPC
Interface, rear	MPO
Polarity	Method A
Total Fibers, quantity	24
Total Ports, quantity, front	24

Dimensions

Height	13.21 mm 0.52 in
Width	159.77 mm 6.29 in
Depth	130.3 mm 5.13 in

NG4-MMDC20R000

Outline Drawing



Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM4, bend insensitive

Environmental Specifications

Operating Temperature	-5 °C to +40 °C (+23 °F to +104 °F)
Storage Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 85%, non-condensing

Packaging and Weights

Packaging quantity	1
Packaging Type	Bag Carton