

760250808 | 20" 4G and mmWave base - 68" Tall Base



Round 20 inch diameter by 68" Tall, Integrated Pole Base Concealment Pole for 4G/5G deployments, to house and conceal multiple radios and any other wireless infrastructure equipment in the base of the pole.

- Intended to house and conceal multiple radios and any other wireless infrastructure equipment in a cabinet at the base of the pole
- Includes everything needed for a low to mid power 4G/5G outdoor small cell site
- Concealment integrates AC load center/OVP and disconnect

Meets City of Denver and surrounding area standards

Available with:

- Round Straight 10.75" shaft (default configuration)
- Round Straight 12.75" Integrated Shaft with space for additional equipment

Utilizes Milbank meter can "U4801-XC-5T9"

OBSOLETE

Replaced By:

760252850

Round 20 inch diameter, Integrated Pole Base Concealment Pole for 4G/5G deployments, to house and conceal multiple radios and any other wireless infrastructure equipment in the base of the pole.

Product Classification

Product Type	Integrated pole
Product Brand	Metro Cell
Ordering Note	ANDREW® standard product with terms
Warranty	One year

General Specifications

Antenna Compatibility, ANDREW	ANDREW Canister Antennas
Antenna Compatibility, Other Vendors	ACE AMPHENOL GALTRONICS GAMMA NU JMA KATHREIN KMW ROSENBERGER mmWave active antennas
Antennas Included	None
Color	Light Gray (RAL 7035)
Color Options	Beige-Grey (RAL 7006) Black (RAL 9005) Black Green (RAL 6012) Brown (RAL 8014) Faux Concrete Green (RAL 6005) Metallic Silver Umbra Grey (RAL 7022)

760250808 | 20" 4G and mmWave base - 68" Tall Base

Compatible Foundation Type	Poured Concrete Pre-Cast Concrete
Compatible Smart Devices	Cameras Digital Signage Emergency Call Station Environmental Monitoring Security Lighting WIFI
Cooling	Fan Cooling
Power Supply Compatibility	ABB CC1600 DELTA 2.0 FPAE PSU-AC-08
Radio Compatibility, Ericsson	1281 220x 440x 4449 4455 6701 8843 Diplexer Power Distribution
Radio Compatibility, Nokia	AHFIA AHFIB AHIA AHIB AHLBA AHLBBA AZRB Airscale micro Diplexer Power Distribution Up to (4) AirScale micro radios
Radios Included	None

Dimensions

Height	1,727.2 mm 68 in
Pole Height Options	10.668 m 35 ft 12.192 m 40 ft 6.096 m 20 ft 7.62 m 25 ft 9.144 m 30 ft
Width	508 mm 20 in
Depth	508 mm 20 in
Depth Note	Round

Electrical Specifications

Power/Fiber Input	AC load center with OVP and disconnect
Voltage	120 Vac 240 Vac

Material Specifications

Finish Aluminum	Chromate
Finish Concealment Covers	Powder coated
Material Type	Galvanized steel Steel

Environmental Specifications

Thermal Compliance	GR-487
---------------------------	--------