

760252934 | 26" Pole Cab with Round Tapered Pole



Bottom of the Pole, 26in Square base with round tapered shaft 4G/5G /mmWave Concealment Enclosure to house and conceal multiple low to high power radios and other wireless infrastructure equipment in a cabinet at the base of the pole.

- Intended to house and conceal multiple radios and any other wireless infrastructure equipment in a cabinet at the base of the pole
- Flexible configuration accepts low to high-power single or dual band radios, Integrated AC load center/OVP and Disconnect and integrated AC/DC rectifier options

Supports 4G and mmWave/5G mounting, luminaire arms.

OBSOLETE

Product Classification

Product Type	Pole cab
Product Brand	Metro Cell
Ordering Note	ANDREW® standard product with terms
Warranty	One year

General Specifications

Color	Light Gray (RAL 7035)
Color Options	Beige-Grey (RAL 7006) Black (RAL 9005) Black Green (RAL 6012) Brown (RAL 8014) Faux Concrete Green (RAL 6005) Metallic Silver Umbra Grey (RAL 7022)
Compatible Foundation Type	Poured Concrete Pre-Cast Concrete
Compatible Smart Devices	Cameras Digital Signage Emergency Call Station Environmental Monitoring Security Lighting WIFI
Cooling	Fan Cooling
Power Supply Compatibility	ABB CC1600 CCI PSU-1200W-48-N DELTA 2.0 PSU-AC-08
Radio Compatibility, Ericsson	(1) 8843/4449 dual-band high power radio and (2) PSU-AC08 (2) RRUS11/12/32, 2212, 4415, 4426, 4478 (base) (3) 2203/2205/2208 (Pole Top) 220x 440x Power Distribution
Radio Compatibility, Nokia	(2) Airscale dual band radios (160W or 320W and (2) Delta 1kW rectifiers (base) AHFIA AHFIB AHIA AHIB AHLBA AHLBBA AZRB Airscale micro Power Distribution
Radio Compatibility Samsung	DELTA 2.0 GE Power Distribution RF4402D-D1A RT2201-46A RT4401-48A

760252934 | 26" Pole Cab with Round Tapered Pole

Radios Included None

Dimensions

Height Note 4 ft tall Equipment Cabinet Base

Pole Height Options 10.668 m | 35 ft | 9.144 m | 30 ft

Width 660.4 mm | 26 in

Depth 660.4 mm | 26 in

Depth Note Square

Pole Diameter 203.2 mm | 8 in

Electrical Specifications

Power/Fiber Input AC load center with OVP and disconnect

Material Specifications

Finish Aluminum Chromate

Finish Concealment Covers Powder coated

Material Type Steel

Environmental Specifications

Thermal Compliance GR-487