

# BTT-B8HA000000N000

---



BTT Tap Terminal, 8 Port, Hardened full size, butt type, 90/10 configuration, black

- Full and terminating tap versions
- Available in both butt and Inline configurations
- Available in both black and gray housing color
- Color coded ports for identification easiness

## Product Classification

<b>Regional Availability</b>	Latin America
<b>Product Type</b>	Access terminal, with tap
<b>Product Series</b>	BTT
<b>Minimum Order Quantity</b>	1

## General Specifications

<b>Cable Type</b>	No cable (stubless)
<b>Distribution Type</b>	8-port tap
<b>Drop Port Type</b>	Hardened full-size SC/APC
<b>Drop Port, quantity</b>	8
<b>Enclosure Color</b>	Black
<b>Forward Port Type</b>	Hardened full-size SC/APC adapter
<b>Forward Port, quantity</b>	1
<b>Input Tap, quantity</b>	1
<b>Mounting</b>	Handhole   Pedestal   Pole   Strand
<b>Port Type</b>	Hardened full-size SC/APC
<b>Port, quantity</b>	10
<b>Split Ratio</b>	90/10
<b>Splitter, quantity</b>	1
<b>Stub Type</b>	No tail

## Dimensions


<b>Width</b>	141 mm   5.551 in
<b>Depth</b>	90 mm   3.543 in

# BTT-B8HA000000N000


**Length** 258 mm | 10.157 in

**Cable Length, stub** 0 ft (0 m)

## Port Configuration



## Ordering Tree



Ordering example  
 Hardened Full Tap, Black, Butt, 70/30 (BTT-B8H0D00000N000)

## Material Specifications

**Enclosure Material Type** Glass filled polypropylene (GF-PP)

## Optical Specifications

**Fiber Type** G.657.A2  
**Operating Wavelength Range** 1260 – 1650 nm  
**Tap Drop Loss, maximum** 21.54 dB  
**Tap Thru Loss, maximum** 0.73 dB

## Environmental Specifications

# BTT-B8HA000000N000

---

<b>Operating Temperature</b>	-30 °C to +70 °C (-22 °F to +158 °F)
<b>Relative Humidity</b>	0%–100%, condensing
<b>Environmental Space</b>	Above ground   Below ground   Buried
<b>Qualification Standards</b>	Anatel
<b>UV Resistance</b>	UV stabilized

## Packaging and Weights

<b>Packaging quantity</b>	1
<b>Packaging Type</b>	Box   Carton

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

