

# 760249191 | 26" Pole Cab with 12" Integrated Pole Shaft



Pole Cab with an Integrated Pole supporting 4G/5G/mmWave technologies as well as smart devices

- Intended to house and conceal multiple radios and any other wireless infrastructure equipment in a cabinet at the base of the pole
- Flexible configuration accepts low to high-power single or dual band radios, Integrated AC load center/OVP and Disconnect and integrated AC/DC rectifier options

Also available with a 30"x30" base for additional capacity  
-Multi Carrier capable

**OBSOLETE**

## Product Classification

<b>Product Type</b>	Pole cab
<b>Product Brand</b>	Metro Cell
<b>Ordering Note</b>	ANDREW® standard product with terms
<b>Warranty</b>	One year

## General Specifications

<b>Antenna Compatibility, ANDREW</b>	ANDREW Canister Antennas
<b>Antenna Compatibility, Other Vendors</b>	ACE   AMPHENOL   GALTRONICS   GAMMA NU   JMA   KATHREIN   KMW   ROSENBERGER
<b>Antennas Included</b>	None
<b>Color</b>	Light Gray (RAL 7035)
<b>Color Options</b>	Beige-Grey (RAL 7006)   Black (RAL 9005)   Black Green (RAL 6012)   Brown (RAL 8014)   Faux Concrete   Green (RAL 6005)   Metallic Silver   Umbra Grey (RAL 7022)
<b>Compatible Foundation Type</b>	Poured Concrete   Pre-Cast Concrete
<b>Compatible Smart Devices</b>	Cameras   Digital Signage   Emergency Call Station   Environmental Monitoring   Security Lighting   WIFI
<b>Cooling</b>	Fan Cooling
<b>Power Supply Compatibility</b>	DELTA 2.0   PSU-AC-08
<b>Radio Compatibility, Ericsson</b>	(1) 8843/4449 dual-band high power radio and (2) PSU-AC08   1281   220x   440x   4426   4478   6701   Power Distribution
<b>Radio Compatibility, Nokia</b>	AEUB   AEWB   AEWB /AEWE   AHFB   AHFIA   AHFIB   AHIA   AHIB   AHLBA   AHLBBA   AZRB   Airscale

Page 1 of 2

# 760249191 | 26" Pole Cab with 12" Integrated Pole Shaft

---

micro

## Radio Compatibility Samsung

AT1K01 | AT1K02 | AT1K0X | Diplexer | HT1K01 | Power Distribution | RF4402D-D1A | RFV01U-D1A | RFV01U-D2A | RT2201-46A | RT4401-48A

## Radios Included

None

## Dimensions

### Height Note

4 ft tall Equipment Cabinet Base

### Pole Height Options

10.668 m | 35 ft

### Width

660.4 mm | 26 in

### Depth

660.4 mm | 26 in

### Depth Note

Square

### Pole Diameter

323.85 mm | 12.75 in

## Electrical Specifications

### Power/Fiber Input

AC load center with OVP and disconnect

## Material Specifications

### Finish Aluminum

Chromate

### Finish Concealment Covers

Powder coated

### Material Type

Galvanized steel

## Environmental Specifications

### Thermal Compliance

GR-487