

NOTES:

1.0 GENERAL NOTES

- 1.1 ALL METRIC DIMENSIONS ARE IN BRACKETS [X. X]
- 1.2 MARK PART WITH IDENTIFICATION NUMBER
- 1.3 FOR PATENT INFO: <https://www.cs-pat.com>

2.0 DESIGN NOTES

3.0 MANUFACTURING/SPECIAL REQUIREMENTS



- 3.1 TIGHTEN ALL BOLTS SECURING FLAT PLATES BY THE TURN-OF-NUT METHOD. TIGHTEN ALL U-BOLTS USING TURN-OF-NUT METHOD WITH ATTENTION TO LEAVE EQUAL DISTANCE AND EQUAL FORCE ON EACH LEG OF THE U-BOLT.

4.0 TEST

5.0 PACKAGING

- 5.1 PACKAGING SHALL MEET COMMSCOPE REQUIREMENTS PER DOCUMENT IS-PL-3005
- 5.2 PRINTED DOCUMENT TO BE PLACED INSIDE POLYBAG AND THEN IN SHIPPING CONTAINER
- 5.3 EXTRA HARDWARE MAYBE SUPPLIED, BAGGED AND SHIPPED

REVISIONS				
REV.	ECN	DESCRIPTION	BY	DATE
A	14016	INITIAL RELEASE	YMENG	08/06/2021
B	15809	REMOVED SURVIVAL WIND SPEED NOTE REPLACED TORQUE NOTES WITH GENERAL TORQUE NOTES REPLACED VCP WITH MTC4104-0018	YMENG	10/25/2021



ITEM	PART NO.	DESCRIPTION	QTY.	NOTE NO.
1	L3325	ANGLE, CROSSOVER MOUNTING	1	
2	MTC4104-0018	CLAMP HALF, 2.0	1	
3	GB-05605	5/8" X 6" GALV BOLT KIT	2	
4	GWF-05	5/8" GALV FLAT WASHER, 1.7OD	6	
5	GB-05205	5/8" X 2" GALV BOLT KIT	2	

DENSITY		lbs/in <sup>3</sup>
MASS	36.15	lbs
VOLUME	127.22	in <sup>3</sup>
SURFACE AREA	1048.10	in <sup>2</sup>
HEIGHT		
LENGTH		
WIDTH		

**COMMSCOPE, INC. OF NORTH CAROLINA**

TOLERANCES		SAP MATERIAL MASTER						
0 PLACE X ± .25	2 PLACE .XX ± 0.06	<b>VZWSMART-MSK7</b>						
1 PLACE .X ± 0.12	ANGLES ± 2°							
FINISH GALV A123		MATERIAL A36; A529						
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES INTERPRET PER ANSI Y 14.5M-1994		NAME	DATE	<b>ANGLE TO ANGLE CROSSOVER KIT</b>				
		CE YMENG	08/06/2021					
		RW YMENG	10/25/2021					
		AD BCROSS	10/27/2021					
		RE HDAI	10/27/2021					
ECN 15809PC	SCALE <b>1:4</b>	DOCUMENT NO. <b>VZWSMART-MSK7</b>						
SIZE	Auth Group	INSL	MODEL	DRAWING		SHEET <b>1 OF 1</b>		
<b>C</b>			VERSION	STATUS	REVISION		VERSION	STATUS
	01	RE	B	01	RE	B		