


MC-PM12M-15C-WLL



ATLAS 12 ft Monopole Platform with (15) 2.88" OD x 120" Antenna Pipes.
Includes Top Rail Kit.

The innovative ATLAS Monopole Platform provides high-load performance, Lower EPA, and reduced weight – all with a single-point tower connection.

NOTE: Engineering loading based on Antenna pipes vertically centered on main horizontal face.

Product Classification

Product Type Monopole platform kit

General Specifications

Mounting Monopole, 304.8–1270 mm (12–50 in) OD

Pipe, quantity 15

Sectors, quantity 3

Dimensions

Height 3,048 mm | 120 in

Face Width 3.81 m | 12.5 ft

Platform Width 3,810 mm | 150 in

Width 3,810 mm | 150 in

Pipe Length 3,048 mm | 120 in

Face Support Pipe Diameter 73.025 mm | 2.875 in

Mounting Diameter, maximum 1,143 mm | 45 in

Mounting Diameter, minimum 304.8 mm | 12 in

Pipe Outer Diameter 73.025 mm | 2.875 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact steelproducts@commscope.com or call 800-255-1479

Wind Rating Test Method TIA/EIA-222

MC-PM12M-15C-WLL

Packaging and Weights

Included Plain end pipes | Platform | Rail | Ring mount

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant



* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code