STT-B1HE00000HN000



STT, NOVUX™ Specialty Tap Terminal, 1 Drop port, 80/20, Stubless with Full-size Adapters

- NOVUX™ Hardened Multi-fiber Terminals incorporate hardened connector technology that is designed to withstand the rugged outside plant environment
- Hardened connectors are factory-integrated and environmentally sealed for use in optical drop cable deployments
- Plug and play adapter ports ensure rapid cable installment in the outside plant access section of the network
- NOVUX™ STT terminals are available with 1 drop port for connection to a splitter terminal and 1 forward port
- Stubless terminal with hardened Input port
- NOVUX™ smaller terminal size allowing for installation in constrained spaces
- NOVUX™ terminals are available in Black (RAL# 9005) or Gray (RAL# 7035)
- CommScope Product ID plate with QR code link to product documents and C-Track

Product Classification

Regional Availability Asia | EMEA | Latin America | North America

Product Type Access terminal, with tap

Product Brand NOVUX™

Product Series STT

Minimum Order Quantity

General Specifications

Cable Type No cable (stubless)

Distribution Type 1-port tap

Drop Port TypeHardened full-size SC/APC

Drop Port, quantity

Enclosure Color Black (RAL 9005)

Multi-fiber Port Type Hardened multi-fiber (HMFOC) jack, male/pinned

Input Tap, quantity 1

Mounting Handhole | Pedestal | Pole | Strand

Port Type Hardened full-size SC/APC

Split Ratio 80/20

Splitter, quantity

Stub Type No tail

COMMSCOPE®

STT-B1HE00000HN000

Tap Ports, quantity

Thru Tap, quantity

Dimensions


 Height
 244 mm | 9.606 in


 Width
 99 mm | 3.898 in

 Length
 64 mm | 2.5 in

Cable Length, stub 0 ft (0 m)

Dimension Drawing





Material Specifications

Enclosure Material Type Hardened plastic

Optical Specifications

Operating Wavelength Range 1260 – 1635 nm

Attenuation Single Ports, maximum 10 dB

COMMSCOPE®

STT-B1HE00000HN000

Tap Drop Loss, maximum8.2 dBTap Thru Loss, maximum1.7 dB

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +65 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +149 \,^{\circ}\text{F})$

Relative Humidity 5%-100%, condensing

Environmental Space Above ground | Below ground

Qualification Standards IEC 60529, IP68 + 2 m waterhead | IEC 61753-1, category G

UV Resistance UV stabilized

Packaging and Weights

Packaging quantity 1

Packaging Type Box

Regulatory Compliance/Certifications

AgencyClassificationCHINA-ROHSBelow maximum concentration valueISO 9001:2015Designed, manufactured and/or distributed under this quality management systemREACH-SVHCCompliant as per SVHC revision on www.commscope.com/ProductComplianceROHSCompliantUK-ROHSCompliant

