## SXT-B2HB00000MN000



SXT, NOVUX<sup>™</sup> Specialty Indexing Terminal, Full-size, Index Only with Reverse (HMFOC Jack/male/pinned), Stubless with HMFOC Jack (male/pinned) Input

- NOVUX™ Hardened Multi-fiber Terminals incorporate hardened connector technology that is designed to withstand the rugged outside plant environment
- Hardened connectors are factory-integrated and environmentally sealed for use in optical drop cable deployments
- Plug and play adapter ports ensure rapid cable installment in the outside plant access section of the network
- NOVUX™ SXT terminals are available in 1 to 2 ports for Index and Branch applications
- Available with flat dielectric and flat toneable/locatable dielectric cable
- NOVUX™ smaller terminal size allowing for installation in constrained spaces
- NOVUX™ terminals are available in Black (RAL# 9005) or Gray (RAL# 7035)
- CommScope Product ID plate with QR code link to product documents and C-Track

#### Product Classification

Regional Availability Asia | EMEA | Latin America | North America

**Product Type**Access terminal, without splitter/tap

**Product Brand** NOVUX<sup>™</sup>

Product Series SXT

Minimum Order Quantity

### General Specifications

Cable Type No cable (stubless)

**Distribution Type** 2 ports

**Drop Port Type**Hardened full-size SC/APC

Drop Port, quantity

**Enclosure Color** Black (RAL 9005)

Forward Port Type Hardened multi-fiber (HMFOC) jack, male/pinned

Forward Port, quantity

Multi-fiber Port Type Hardened multi-fiber (HMFOC) jack, male/pinned

Multi-fiber Port, quantity 2

Mounting Handhole | Pedestal | Pole | Strand

Port Type Hardened full-size SC/APC

COMMSCOPE®

# SXT-B2HB00000MN000

Port, quantity 4

Reverse Port Type Hardened full-size SC/APC

Reverse Port, quantity

Stub Type No tail

**Dimensions** 


 Height
 244 mm | 9.606 in


 Width
 99 mm | 3.898 in

 Length
 64 mm | 2.5 in

Cable Length, stub 0 ft (0 m)

### Dimension Drawing





## Material Specifications

**Enclosure Material Type** Hardened plastic

**Optical Specifications** 

**Operating Wavelength Range** 1260 – 1635 nm

Page 2 of 3

# SXT-B2HB00000MN000

**Attenuation Single Ports, maximum** 0.4 dB **Return Loss, Connector, typical** 65 dB

### **Environmental Specifications**

**Operating Temperature**  $-40 \,^{\circ}\text{C} \text{ to } +65 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +149 \,^{\circ}\text{F})$ 

**Relative Humidity** 5%-100%, condensing

Environmental Space Above ground | Below ground

**Qualification Standards** IEC 60529, IP68 + 2 m waterhead | IEC 61753-1, category G

**UV Resistance** UV stabilized

Packaging and Weights

Packaging quantity 1
Packaging Type Box

## Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

