

HST, NOVUX™ Prodigy™ Hardened Standard Terminal, 2-port Planar 1:2 Splitter, Dielectric flat loose tube cable, 1200 ft/365 m

- NOVUX[™] Prodigy[™] Hardened Multi-port Terminals incorporate Hardened connector technology that is designed to withstand the rugged outside plant environment
- Hardened connectors are factory-integrated and environmentally sealed for use in optical drop cable deployments
- Plug and play adapter ports ensure rapid cable installment in the outside plant access section of the network
- NOVUX[™] Prodigy[™] HST terminals are available with 2 to 12 ports and can be utilized in Single Fiber Point-to-Point (P2P) solutions
- Available with flat dielectric, flat toneable/locatable dielectric, armored or 5mm round cable
- NOVUX[™] Prodigy[™] smaller terminal size for aesthetics and allowing installation in constrained spaces
- NOVUX[™] Prodigy[™] terminals are available in Black (RAL# 9005) or Gray (RAL# 7035)
- CommScope Product ID plate with QR code link to product documents and C-Track

Product Classification

Regional Availability	Asia EMEA Latin America North America	
Product Type	Access terminal, with splitter/tap	
Product Brand	NOVUX™	
Product Series	HST	
Minimum Order Quantity	1	
General Specifications		
Cable Type	Dielectric - Flat - Loose Tube	
Cable, quantity	1	
Distribution Type	1 x 2 splitter	
Drop Port Type	Hardened Prodigy SC/APC	
Drop Port, quantity	2	
Enclosure Color	Black (RAL 9005)	
Mounting	Handhole Pedestal Pole Strand	
Port Type	Hardened Prodigy SC/APC	
Port, quantity	2	
Splitter, quantity	1	
Stub Type	Stub tail	


Page 1 of 4



Dimensions

80 mm 3.15 in
79 mm 3.11 in
161 mm 6.339 in
1200 ft (365 m)
4.3 x 8.0 mm (0.17 x 0.31 in)

Dimension Drawing



Port Configuration


161 mm

NOVUX HT	TECHNOLOGIES AVAILABLE	SMALL	MEDIUM	LARGE
HST Series	Single-fiber: P2P/no splitters	2 ports	6 ports	12 ports
		4 ports	8 ports	
	Single-fiber: P2P w/splitters	2 ports, 1x1:2	8 ports, 2x1:4	12 ports, 3x1:4
		4 ports, 1x1:4	8 ports, 1x1:8	
	Hybrid for multi-use		7 ports, 1x1:4 splitter, 3 P2P	12 ports, 1x1:8 splitter, 4 P2P
		4 ports, 1x1:2 splitter, 2 P2P	8 ports, 1x1:4 splitter, 4 P2P	11 ports, 2x1:4 splitter, 2 P2P, 1 HMFOC 4f

Ordering Tree

Page 2 of 4





Material Specifications

Optical Specifications
Fiber Type G.657.A1/A2
Operating Wavelength Range 1260 – 1635 nm
Attenuation Single Ports, maximum4.1 dB
Attenuation Cable Coefficient, maximum0.30 dB/km @ 1550 nm0.40 dB/km @ 1310 nm
Attenuation Splitter, maximum3.7 dB
Attenuation Terminal Connectors, maximum0.4 dB
Return Loss, Single Ports, minimum 55 dB

Environmental Specifications

Operating Temperature	-40 °C to +65 °C (-40 °F to +149 °F)
Relative Humidity	5%–100%, condensing

Page 3 of 4



Compliant

Compliant

REACH-SVHC

ROHS

UK-ROHS

Environmental Space	Above ground Below ground			
Qualification Standards		IEC 61753-1, category G IEC 61753-111-08 (this represents an IEC 60529 IP68 intrusion protection level)		
UV Resistance		UV stabilized		
Packaging and Weights				
Packaging quantity		1		
Packaging Type		Box Universal spool, cardboard: terminal is on top of the spool, stub deploys first		
Regulatory Compliance/Certifications				
Agency	Classification			
CHINA-ROHS	Below maximum concentration value			
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system			

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Page 4 of 4

