







- NOTES:
- 1.0 GENERAL
    - 1.1 ALL METRIC DIMENSIONS ARE IN BRACKETS
    - 1.2 MARK PART WITH IDENTIFICATION NUMBER
    - 1.3 FOR PATENT INFO: <https://www.cs-pat.com>
  - 2.0 DESIGN NOTES
  - 3.0 MANUFACTURING/SPECIAL REQUIREMENTS
    - 3.1 TIGHTEN ALL BOLTS SECURING FLAT PLATES BY THE TURN-OF-NUT METHOD. TIGHTEN ALL U BOLTS USING TURN-OF-NUT METHOD WITH ATTENTION TO LEAVE EQUAL DISTANCE AND EQUAL FORCE ON EACH LEG OF THE U-BOLT.
  - 4.0 TEST
  - 5.0 PACKAGING
    - 5.1 PACKAGING SHALL MEET COMMSCOPE REQUIREMENTS PER DOCUMENT IS-PL-3005
    - 5.2 PRINTED DOCUMENT TO BE PLACED INSIDE POLYBAG AND THEN IN SHIPPING CONTAINER
    - 5.3 EXTRA HARDWARE MAYBE SUPPLIED BAGGED AND SHIPPED

REVISIONS				
REV.	ECN	DESCRIPTION	BY	DATE
A	15839	INITIAL RELEASE	MAC	2021/9/14
B	15839	UPDATED FOR EQP0404L-DSH CHANGE	MAC	2022/1/5




DETAIL D  
SCALE 1 : 6

SOME FIELD FITTING MAY BE REQUIRED IF STAIRCASE & LANDING, OR SHIPS LADDER WILL BE USED.



DETAIL E  
SCALE 1 : 6



DETAIL F  
SCALE 1 : 8

BOM IS FOR REFERENCE ONLY, PART NUMBER SUBSTITUTIONS MAY BE MADE

ITEM	PART NO.	DESCRIPTION	QTY.	WEIGHT	NOTE NO.
1	EQPHR-6000	RECTANGLE TUBE, HANDRAIL	2	8.16 LBS	
2	EQPHR-7000	RECTANGLE TUBE, HANDRAIL	2	8.56 LBS	
3	EQPTB-5000	TOEBOARD	2	7.89 LBS	
4	TS1288	12-24 X 7/8" SELF DRILLING SCREW	8	0.01 LBS	
5	MTC3979HR19	ANGLE BRKT, HANDRAIL	2	0.32 LBS	
6	MTC4037HR21	FORMED ANGLE, HANDRAIL STIFFENER	2	2.08 LBS	
7	MTC403721	POST, HANDRAIL	4	9.98 LBS	
8	GB-03105	3/8" X 1" GALV BOLT KIT	12	0.05 LBS	
9	GB-03165	3/8" X 1-3/4" GALV BOLT KIT	8	0.07 LBS	
10	GB-03205	3/8" X 2" GALV BOLT KIT	4	0.08 LBS	
11	GWF-03	3/8" GALV FLAT WASHER	12	0.01 LBS	

DENSITY	0.28	lbs/in <sup>3</sup>
MASS	96.26	lbs
VOLUME	341.45	in <sup>3</sup>
SURFACE AREA	5721.24	in <sup>2</sup>
HEIGHT	48.788	
LENGTH	56.515	
WIDTH	64.918	

© 2021 CommScope, Inc. Confidential

COMMSCOPE, INC. OF NORTH CAROLINA

TOLERANCES		SAP MATERIAL MASTER																
1 PLACE .X ± 0.25	3 PLACE .XXX ± 0.06	EQP0404LHR-DSH																
2 PLACE .XX ± 0.12	ANGLES ± 2°																	
FINISH GALV A123		MATERIAL SEE BOM																
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES INTERPRET PER ANSI Y 14.5M-1994		TITLE 48" x 48" Hand-Rail for Elevated LD																
<table border="1"> <thead> <tr> <th>NAME</th> <th>DATE</th> <th>TITLE</th> </tr> </thead> <tbody> <tr> <td>CE MAC</td> <td>10/10/2021</td> <td></td> </tr> <tr> <td>RW MM1298</td> <td>03/16/2022</td> <td></td> </tr> <tr> <td>AD BA1025</td> <td>03/16/2022</td> <td></td> </tr> <tr> <td>RE MM1298</td> <td>03/16/2022</td> <td></td> </tr> </tbody> </table>		NAME	DATE	TITLE	CE MAC	10/10/2021		RW MM1298	03/16/2022		AD BA1025	03/16/2022		RE MM1298	03/16/2022		SCALE 1:16	
NAME	DATE	TITLE																
CE MAC	10/10/2021																	
RW MM1298	03/16/2022																	
AD BA1025	03/16/2022																	
RE MM1298	03/16/2022																	
ECN 15839PC		DOCUMENT NO. EQP0404LHR-DSH																
SIZE Auth Group INSL	MODEL	DRAWING																
C	01 RE B	VERSION	STATUS															
		REVISION	REVISION															
		01	RE B															
SHEET			1 OF 1															