

NOVUX[™] Specialty Range Closure 100, splice only, no adapters, no splitters, 12 splices, SMOUV® 45mm splice protectors, black, (HMFOC) cable assembly, HMFOC plug to stub, 12-fiber 20FT.Gel-filled, TelSplice connector

- Modern drop solution offering providers the agility and flexibility to use it in last-mile fiber network applications, both above and below ground
- Protected from harsh conditions by CommScope's Octopus gel sealing technology
- Agnostic to connectivity technologies: splice, connector, field-installable connector for agility and flexibility
- Identification plate for either QR code or customer logo
- QR code and CommScope cTrak® app for one-click access to all product information

Product Classification

| Regional Availability | Asia EMEA Latin America North America |
|---|--|
| Regional Availability Note | Contact your local CommScope representative for specific availability |
| Product Type | Single-ended, rectangular fiber closure |
| Product Brand | NOVUX™ |
| Product Series | SRC100 |
| General Specifications | |
| Cable Capacity, Drop | 4 Flat 8.0 x 4.5 mm (0.30 x 0.17 in) 4 Round 1.2–8.0 mm (0.05–0.31 in) |
| Cable Ports Quantity, total | 4 multi-out ports (8 cables) |
| Cable Sealing Type | Compressed gel |
| Cable Termination Attachments, quantity | 2 |
| Closure Sealing Type | Hinged with latch |
| Closure Style | Single-ended |
| Color | Black |
| Mounting | Handhole Partially buried Pedestal Wall/Pole Mount, mounting kit included |
| Network Area Type | Drop |
| Port Type | No adapter No adapter |
| Port, quantity | 0 |
| Splice Tray Included, quantity | 1 |

Page 1 of 4

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: July 14, 2023




| Splice Tray Type Included | 12-way, heat shrink |
|---|---------------------|
| Splicing Capacity, maximum | 12 |
| Splicing Capacity, Single Fusion, maximum | 12 |
| Splicing Type, Supported | Single fusion |
| Splitter Type | No splitter |
| Splitter, quantity | 0 |
| Dimensions | |
| Height | 267 mm 10.512 in |
| Width | 117 mm 4.606 in |
| Depth | 49 mm 1.929 in |
| Cable Entry Drop Port Diameter | 8 mm (0.31 in) mm |

Ordering Tree

Page 2 of 4

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: July 14, 2023





Material Specifications

| Material Type | Impact-resistant polymer |
|------------------------------|---|
| Optical Specifications | |
| Fiber Type | G.652.D G.657.A1 G.657.A2 G.657.B3 |
| | |
| Environmental Specifications | |
| Operating Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |
| Environmental Space | Above ground Below ground Direct burial |
| Qualification Standards | IEC 60529, IP68 + 2 m waterhead IEC 61753-1, category G |
| UV Resistance | UV stabilized |

Page 3 of 4

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: July 14, 2023

COMMSCOPE°

| Flash test valve at 2 psi (20 kPa) |
|---|
| |
| 10 |
| Box Carton |
| |
| per Splice Tray Tone Wire Connector |
| " Cable Termination Unit (CTU) for flat cables with 3x5 to 4x8 mm diameter, metal |
| * Cable Termination Unit (CTU) for round cables with 4 to 6,2 mm diameter, metal |
| |

Page 4 of 4

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: July 14, 2023

